

TYPE ILCB-12-LIO

Features

- 18 Volt battery
- Lithium-Ion technology
- 70% more crimp cycles than Ni-Cad
- Battery powered
- Accepts IlSCO standard "U" dies
- Ram automatically retracts when crimp cycle is complete
- Automatic retraction stop which retracts the ram just enough to get ready for the next cycle
- Head rotates 360 degrees
- Pistol grip design
- Molded-in rubber grip
- Quick charge 120 volt charger
- Two 18 volt batteries included
- LED work light
- Diagnostics built in

Benefits

- Powerful, quick crimp, saves time
- Faster, longer life, quicker charge, lighter
- More crimps between charges
- Portable, can be used in any location
- Precision crimps
- Confirms crimp is complete
- Saves time and energy
- Adapts to variable cable directions
- Easy to handle and operate
- Provides non-slip comfortable grip
- Less down time
- Rotate batteries, keep working on job
- Lights up dark enclosures/cabinets
- Can retrieve tool statistics (ie: # of crimps)

Specifications

Force developed:	12 Tons
Weight:	14.9 lbs.
Overall length:	16-3/4"
Jaw Opening:	1.65"
Conductor Range:	750kcmil-8 AL 1000kcmil-8 CU



For Use with*

Aluminum Connectors	Copper Connectors
CPM Series	CLN4, CLN9, CLND, CSLT, CLWU
ACM Series	CLNF, CLNN, CLNS,
ACO Series	CLNU, CLW4, CLW9,
ACO-90 Series	CLWD, CLWF, CLWN,
ACL, ACN Series thru 750kcmil	CLWS, CSN4, CSN9,
2ACL, 2ACN Series thru 750kcmil	CSND, CSNF, CSNN,
AS Series thru 750kcmil	CSNS, CSW4, CSW9,
AH 1-4	CSWD, CSWF, CSWN,
HT Series	CSWS thru 1000kcmil
IACL Series thru 750kcmil	
2IACL Series thru 750kcmil	
Series: ALNS, ALND, ASN,	
ALNN thru 750kcmil	

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

*See page 405 for required compression dies

Includes:

- 2 Batteries
- 1 Battery Charger
- Durable Plastic Carrying Case
- Instruction Manual