

## M30



### General data

<b>Switching distance</b>	10 mm,	<b>Housing material</b>	CuZn, chrome-plated
<b>Ambient temperature</b>	-25...+70 °C	<b>Adjustment</b>	Potentiometer

### Types and data – selection table

Type	Connection	Operating voltage	Output	Operating current [mA]	Dimensions	w	d
BC10-M30K-VP4X-H1141	male, M12 x 1	10...65 VDC	, PNP	200,	Ø 30 x 60 mm	w069	d412
BC10-M30K-VP4X	2 m cable	10...65 VDC	, PNP	200,	Ø 30 x 62.5 mm	w067	d413
BC10-M30K-RZ3X	2 m cable	20...250 VAC	, 2-wire	-	Ø 30 x 62.5 mm	w077	d413
BC10-M30K-AZ3X	2 m cable	20...250 VAC	, 2-wire	-	Ø 30 x 62.5 mm	w076	d413

Many different types available, also as NPN version, see type code