

# TURCK

## Level Sensors - Capacitive



Housing Style	Part Number	ID Number	Features	Embeddable Range (mm)	Nonembed. Range (mm)	Output
<b>12 mm - Embeddable, eurofast® Connector</b> 	BC 3-M12-AN6X-0.2M-RS 4T	M2601190		3	3	3-Wire DC NPN
	BC 3-M12-AP6X-0.2M-RS 4T	M2601091		3	3	3-Wire DC PNP
<b>12 mm - Embeddable, Potted-In Cable</b> 	BC 3-M12-AN6X	M2601100		3	3	3-Wire DC NPN
	BC 3-M12-AP6X	M2601000		3	3	3-Wire DC PNP
<b>12 mm - Embeddable, eurofast Connector</b> 	BC 3-S12-AN6X-0.2M-RS 4T	M2601390		3	4.5	3-Wire DC NPN
	BC 3-S12-AP6X-0.2M-RS 4T	M2601291		3	4.5	3-Wire DC PNP
<b>12 mm - Embeddable, Potted-In Cable</b> 	BC 3-S12-AN6X	M2601300		3	4.5	3-Wire DC NPN
	BC 3-S12-AP6X	M2601200		3	4.5	3-Wire DC PNP
	BC 3-S12-AP6X/S100	M2601201	High Temp. 100°C	3	4.5	