

Inductive Cylinder Position Sensors



Housing Style	Part Number	ID	Features	Magnetic Actuation Strength (Gauss)	Output
IKM - eurofast® Connector 	BIM-IKM-AN6X2-H1141/S34 W/KLI-3	M4627390	KLI-3 Included, WFI	20-350	3-Wire DC NPN
	BIM-IKM-AP6X2-H1141/S34 W/KLI-3	M4627290	KLI-3 Included, WFI	20-350	3-Wire DC PNP
IKM - microfast® Connector 	BIM-IKM-AZ3X2-B3131 W/KLI-3	M1347190	KLI-3 Included	20-350	2-Wire AC
IKM - Potted-In Cable 	BIM-IKM-AZ3X2 W/KLI-3	M1347290	KLI-3 Included	20-350	2-Wire AC
	BIM-IKM-AN6X2/S100 W/KLI-3	M4627391	High Temp. 100° C	20-350	3-Wire DC NPN
A23 - eurofast Connector 	BIM-A23-AP6X2-H1141/S34 W/KLU-2	M4689291	KLU-2 Included, WFI	20-350	3-Wire DC PNP



For detailed sensor specifications see Section M.
Normally Closed versions available upon request, consult factory.



Voltage	Switching Freq. (Hz)	Operating Current (mA) VAC/VDC	Operating Temp. (°C)	Protection	Housing	Face	Power LED	Output LED	Mating Cord, Cable Length/Jacket	Wiring Diagram #	Wiring Diagrams
10-30 VDC	20	≤200	-25 to +70	IP 67	Zinc	PA 12	GN	YE	RK 4T-*	1	<p>Diagram 1</p>
10-30 VDC	20	≤200	-25 to +70	IP 67	Zinc	PA 12	GN	YE	RK 4T-*	2	<p>Diagram 2</p>
20-250 VAC	20	≤500	-25 to +70	IP 67	Zinc	PA 12	GN	YE	KB 3T-*	3	<p>Diagram 3</p>
20-250 VAC	20	≤500	-25 to +70	IP 67	Zinc	PA 12	GN	YE	2M/PVC	4	<p>Diagram 4</p>
10-30 VDC	20	≤200	-25 to +100	IP 67	Zinc	PA 12	GN	YE	2M/PVC	1	
10-30 VDC	20	≤200	-25 to +70	IP 67	AL	PBT	GN	YE	RK 4T-*	2	

* Length in meters.

For material descriptions see page M36.