

12, 14 and 19-Pin M16 versafast® Receptacles, Front Mount

- Female Receptacles
- For use with Junction Box Home Run Cables
- IEC IP 67 Protection



Housing Style	Part Number	Lead Specs.	Application	Pinout
	BKF 12-12-*	12x24 AWG 105°C 125 VAC/VDC, 4 A	Mates with 12-pin connectors, 12 conductors	A. BN B. BU C. WH D. GN E. YE F. GY G. PK H. RD J. BK K. OG L. TN M. VT
	BKF 14-10-*	10x24 AWG 105°C 125 VAC/VDC,, 3 A	Mates with 14-pin connectors, 10 conductors	C. GY E. GN G. BK M. BN N. PK O. YE P. WH R. RD S. VT U. BU
	BKF 14-12-*	12x24 AWG 105°C 125 VAC/VDC,, 3 A	Mates with 14-pin connectors, 12 conductors	C. OG E. BK G. GN J. GY M. BN N. TN O. VT P. RD R. WH S. YE T. PK U. BU
	BKF 14-14-*	14x24 AWG 105°C 125 VAC/VDC,, 3 A	Mates with 14-pin connectors, 14 conductors	A. BN C. RD/BU E. BK G. PK J. GN L. BU M. OG N. GY/BN O. VT P. WH R. RD S. GY T. YE U. TN
	BKF 19-19-*	19x24 AWG 105°C 125 VAC/VDC, 3 A	Mates with 19-pin connectors, 19 conductors	A. BU B. GY/PK C. RD/BU D. WH/GN E. BK F. BN/GN G. PK H. WH/YE I. GN K. YE/BN L. BN M. OG N. GY/BN O. VT P. WH R. RD S. GY T. YE U. TN

Receptacles

See page G27 for dimensional drawings.

* Length in meters. Standard lead length is 0.5 Meter. Consult factory for other lengths.

Standard housing material is nickel plated brass.

Available with spanner nut as an option (vs. Hex locknut). Add "/S1046" to end of description.

To specify PVC jacketed cable, add "/S717" to the end of the part number.