


MALE END VIEW



SPECIFICATIONS

HOUSING MATERIAL/PLATING	NYLON/BLACK
CONTACT MATERIAL/PLATING	GOLD/BRASS
COUPLING NUT MATERIAL/PLATING	NICKEL/BRASS
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	125 V
MAXIMUM WIRE SIZE	18 AWG
CABLE GRIP RANGE	4-8mm
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS PROPERTY OF TURCK. NO USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	DATE 11/22/04	DESCRIPTION
			DRWT RDS	BS 8141-0/PG 9
MATERIAL	TOLERANCES UNLESS OTHERWISE SPECIFIED	UNIT OF MEASUREMENT	SCALE 1 = 1.0	IDENTIFICATION NO.
SEE SPECIFICATIONS	0.5 TO 6 ±0.1 6 TO 30 ±0.2 30 TO 200 ±0.3 OVER 200 ±0.4 ANGLES ±1°	MILLIMETERS		U6551
FINISH	SEE SPECIFICATIONS	UNIT OF MEASUREMENT		REP B
SEE SPECIFICATIONS		DO NOT SCALE THIS DRAWING		FILE: U6551

REV	DESCRIPTION	BY	DATE	ECO NO.
B	SUPPLIER CHANGED NUT, UPDATED VIEW, SEE ECO	FWC	09/13/08	18D96