



MALE END VIEW



SPECIFICATIONS

HOUSING MATERIAL/COLOR	MYLON/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	30 VAC/36 VDC
MAXIMUM WIRE SIZE	18 AWG
CABLE GRIP RANGE	5-8mm
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68



SOURCE DRAWING - FOR REFERENCE ONLY

<p>TURCK INC High Technology Sensors and Automation Controls</p>		<p>DATE 06/04/99</p> <p>DESCRIPTION BS B151-0/PG9</p>	<p>FILE: U6570</p>
<p>THIS DRAWING IS PROPERTY OF TURCK. NO USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</p>	<p>DRAWN CBM</p> <p>SCALE 1=1.0</p>	<p>IDENTIFICATION NO. U6570</p>	<p>SHEET 1 OF 1</p>
<p>3RD ANGLE PROJECTION</p>	<p>TOLERANCES UNLESS OTHERWISE SPECIFIED</p> <p>0.5 TO 6 ±0.1 6 TO 30 ±0.2 30 TO 200 ±0.3 OVER 200 ±0.4 ANGLES ±1°</p>	<p>UNIT OF MEASUREMENT MILLIMETERS</p>	<p>DO NOT SCALE THIS DRAWING</p>
<p>RELATED DOCUMENTS</p> <ol style="list-style-type: none"> 1. 2. 3. 4. 	<p>MATERIAL</p> <p>SEE SPECIFICATIONS</p> <p>FINISH</p> <p>SEE SPECIFICATIONS</p>	<p>REV G</p> <p>DATE 09/21/07</p> <p>EDD NO. 18B05</p>	<p>REV DESCRIPTION</p> <p>UPDATE CONTACT PLATING MATERIAL</p>