

3-Wire Cordsets, Standard Duty

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 250 V, 4 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>KB ..**</p>	<p>KB 3T-*</p> <p>WKB 3T-*</p>	<p>SB 3T-*</p> <p>WSB 3T-*</p>	<p>AWM PVC Yellow, 3x22 AWG, 105°C, 5.1 mm OD, Cable #RF50531-*M†</p>	<p>Female</p>
<p>WKB ..**</p>	<p>KB 3T-*/S90</p> <p>WKB 3T-*/S90</p>	<p>SB 3T-*/S90</p> <p>WSB 3T-*/S90</p>	<p>AWM TPU Yellow, 3x18 AWG, 90°C, 5.7 mm OD, Cable #RF50547-*M†, Cut/Abrasion Immune</p>	
<p>KB 3T-*/S105</p> <p>WKB 3T-*/S105</p>	<p>SB 3T-*/S105</p> <p>WSB 3T-*/S105</p>	<p>AWM PVC Yellow, 3x22 AWG, 105°C, 5.7 mm OD, Cable #RF50535-*M†, Braided Shield</p>		
<p>SB ..**</p>	<p>KB 3T-*/S749</p> <p>WKB 3T-*/S749</p>	<p>SB 3T-*/S749</p> <p>WSB 3T-*/S749</p>	<p>AWM PVC Yellow, 2x22 AWG, 105°C, 5.1 mm OD, Cable #RF50650-*M†, 3-pin with 2 conductors</p>	<p>Male</p>
<p>KB 3T-*/S1507</p> <p>WKB 3T-*/S1507</p>	<p>SB 3T-*/S1507</p> <p>WSB 3T-*/S1507</p>	<p>AWM TPE Grey, 3x20 AWG 105°C, 5.7 mm OD, Cable #RF50940-*M†, Flexlife-20, High Flex - Over 20 million cycles</p>		
<p>KB 3T-*/XOR</p> <p>WKB 3T-*/XOR</p>	<p>SB 3T-*/XOR</p> <p>WSB 3T-*/XOR</p>	<p>AWM PVC Yellow, 3x18 AWG, 80°C, 250°C short term, 5.7 mm OD, Cable #RF04159-*M†, Weld Flash Immune, High Temp Immune</p>		

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.
 ** Standard coupling nut material is nickel plated brass "KB .."; "KBK .." indicates nylon and "KBV .." indicates stainless steel.
 † See Section N for **reelfast**[®] cable information.