

TURCK M12 eurofast® Connectivity

8, 10 and 12-Wire Cordsets, "S" Style, Shielded



- Shield to Coupling Nut
- IEC IP 67 Protection
- 60 VAC/75 VDC, 2 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>RKS ..**</p> <p>WKS ..**</p>	<p>RKS 8T-* WKS 8T-*</p>	<p>RSS 8T-* WSS 8T-*</p>	<p>AWM PVC Grey, 8x24 AWG, 105°C, 7.2 mm OD, Cable #RF50813-*M†, RFI/EMI shielding, UL Recognized, CSA Approved</p>	<p>1. WH 2. BN 3. GN 4. YE 5. GY 6. PK 7. BU 8. RD</p>
<p>RKS 10T-* WKS 10T-*</p>	<p>RSS 10T-* WSS 10T-*</p>	<p>AWM PVC Grey, 10x24 AWG, 105°C, 7.2 mm OD, Cable #RF51006-*M†, RFI/EMI shielding</p>	<p>1. WH 2. BN 3. GN 4. YE 5. GY 6. PK 7. BU 8. RD 9. OG 10. TN</p>	
<p>RKS 12T-* WKS 12T-*</p>	<p>RSS 12T-* WSS 12T-*</p>	<p>AWM PVC Grey, 12x24 AWG, 105°C, 7.2 mm OD, Cable #RF50988-*M†, RFI/EMI shielding</p>	<p>1. WH 2. BN 3. GN 4. YE 5. GY 6. PK 7. BU 8. RD 9. OG 10. TN 11. BK 12. VT</p>	

Cordsets

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.
 ** Standard coupling nut material is nickel plated brass "RKS .."; "RKSV .." indicates stainless steel..