

Inductive Rectangular Sensors



Housing Style - Rectangular	Part Number	ID Number	Features	Embeddable	Sensing Range (mm)	Output
	Ni 60-K90-VN4X-B2141	M1520300	Comp. Outputs		60	4-Wire DC NPN
	Ni 60-K90-VP4X-B2141	M1510300	Comp. Outputs		60	4-Wire DC PNP
	Ni 60-K90-AZ3X-B2131	M1354200			60	2-Wire AC

For detailed sensor specifications see Section M.
Normally Closed versions available upon request, consult factory.



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Front Cap/ Face	Power LED	Output LED	Mating Cord	Wiring Diagram #	Wiring Diagrams
10-65 VDC	60	≤200	-25 to +70	IP 67	PUR	PUR	N/A	YE	RK 40-*M	1	<p>Diagram 1</p>
10-65 VDC	60	≤200	-25 to +70	IP 67	PUR	PUR	N/A	YE	RK 40-*M	2	<p>Diagram 2</p>
20-250 VAC	20	≤500	-25 to +70	IP 67	PBT	PBT	N/A	YE	RK 30-*M	3	<p>Diagram 3</p>

Rectangular

For material descriptions see page M36.