



4-Wire Cordsets, Snap Lock (Locking Sleeve)

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 125 V, 2 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>PKG ..Z**</p>	<p>PKG 4Z-* PKW 4Z-*</p>	<p>PSG 4-* PSW 4-*</p>	<p>AWM, PVC Yellow, 4x26 AWG, 105°C, 4.4 mm OD, Cable #RF50697-*M†, flexlife*</p>	<p>Female</p> <p>Male</p>
<p>PKW ..Z**</p>	<p>PKG 4Z-*/S90 PKW 4Z-*/S90</p>	<p>PSG 4-*/S90 PSW 4-*/S90</p>	<p>AWM, TPU Black, 4x26 AWG, 90°C, 4.4 mm OD, Cable #RF50586-*M†, Cut/Abrasion Immune</p>	
<p>PKG 4Z-*/S90/S101 PKW 4Z-*/S90/S101</p>	<p>PSG 4-*/S90/S101 PSW 4-*/S90/S101</p>	<p>AWM, TPU Black, 4x26 AWG, 90°C, 4.4 mm OD, Cable #RF50935-*M†, Cut/Abrasion Immune, flexlife-20, High Flex - Over 20 Million Cycles</p>	<p>1. BN 2. WH 3. BU 4. BK</p>	
<p>PKG 4Z-*/S90/S618 PKW 4Z-*/S90/S618</p>	<p>PSG 4-*/S90/S618 PSW 4-*/S90/S618</p>	<p>AWM, TPU Black, 4x26 AWG, 90°C, 4.4 mm OD, Cable #RF50602-*M†, Cut/Abrasion Immune, EMI/RFI Protection</p>		
<p>PKG 4Z-*/S760 PKW 4Z-*/S760</p>	<p>PSG 4-*/S760 PSW 4-*/S760</p>	<p>AWM, PVC Black, 4x26 AWG, 105°C, 4.4 mm OD, Cable #RF50870-*M†, flexlife</p>		
<p>PKG 4Z-*/S90/S653 PKW 4Z-*/S90/S653</p>	<p>PSG 4-*/S90/S653 PSW 4-*/S90/S653</p>	<p>AWM, TPU Black, 3x24 AWG, 90°C, 4.4 mm OD, Cable #RF50601-*M†, Cut/Abrasion Immune, EMI/RFI Protection</p>	<p>1. BN 2. Drain 3. BU 4. BK</p>	

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters.

** Locking sleeve material is POM.. "PKG..Z".

† See Section N for **reelfast**™ cable information.

Cordsets