

4-Wire *euromast*® Cordsets, "C" Style Medium Plug Body

- Straight Female Connector
- NEMA 1, 3, 4, 6P and IEC IP 68 Protection
- 250 V, 4 A



Housing Style	Part Number	Cable	Features	Pinout
	RKC 4.4T-*	AWM PVC Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50579-*M†	<i>flexlife</i> ®	<ol style="list-style-type: none"> 1. BN 2. WH 3. BU 4. BK
	RKC 4.4T-*/S90	AWM PUR Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50544-*M†	<i>Cut/Abrasion Immune</i>	
	RKC 4.4T-*/S622	AWM PVC Grey 4x18 AWG 105°C 7.3 mm OD Cable #RF50580-*M†	<i>flexlife</i>	
	RKC 4.4T-*/S824	PLTC PVC Grey 4x22 AWG 105°C 5.2 mm OD Cable #RF50698-*M†	<i>Tray Rated</i>	
	RKC 4.4T-*/S1587	AWM TPE Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50956-*M†	<i>Weld Flash Immune</i>	
	RKC 4.4T-*/S101/S849	AWM TPE Grey 4x22 AWG 105°C 5.7 mm OD Cable #RF50941-*M†	<i>flexLife-10, High Flex</i>	
	RKC 4.4T-*/S101	AWM TPE Yellow 4x18 AWG 105°C 7.2 mm OD Cable #RF50968-*M†	<i>Over 10 Million Cycles</i>	
	RKC 4.4T-*/S1062	AWM PVC Yellow 4/18 AWG 105°C 7.3 mm OD Cable #RF50579-*M†	<i>flexlife</i> ® Cable, PVC plug body with PVC contact carriers	

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.
 ** Standard coupling nut material is nickel plated brass "RKC .."; "RKC V .." indicates 316 stainless steel.
 † See Section N for *reelfast*® cable information.

4-Wire *euromast*® Cordsets, "C" Style Medium Plug Body

- Straight Male Connector
- NEMA 1, 3, 4, 6P and IEC IP 68 Protection
- 250 V, 4 A



Housing Style	Part Number	Cable	Features	Pinout
	RSC 4.4T-*	AWM PVC Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50579-*M†	<i>flexlife</i> ®	
	RSC 4.4T-*/S90	AWM PUR Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50544-*M†	<i>Cut/Abrasion Immune</i>	
	RSC 4.4T-*/S622	AWM PVC Grey 4x18 AWG 105°C 7.3 mm OD Cable #RF50580-*M†	<i>flexlife</i>	
	RSC 4.4T-*/S824	PLTC PVC Grey 4x22 AWG 105°C 5.2 mm OD Cable #RF50698-*M†	<i>Tray Rated</i>	
	RSC 4.4T-*/S1587	AWM TPE Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50956-*M†	<i>weldlife, Weld Flash Immune</i>	
	RSC 4.4T-*/S101/S849	AWM TPE Grey 4x22 AWG 105°C 5.7 mm OD Cable #RF50941-*M†	<i>flexLife-10, High Flex Over 10 Million</i>	
	RSC 4.4T-*/S101	AWM TPE Yellow 4x18 AWG 105°C 7.2 mm OD Cable #RF50968-*M†		
	RSC 4.4T-*/S1062	AWM PVC Yellow 4/18 AWG 105°C 7.3 mm OD Cable #RF50579-*M†	<i>flexlife</i> ® Cable, PVC plug body with PVC contact carriers	

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RSC .."; "RSCV .." indicates 316 stainless steel.

† See Section N for *reelfast*® cable information.