


FEMALE END VIEW



- 1 = BROWN
- 2 = WHITE
- 3 = BLUE
- 4 = BLACK



MALE END VIEW




- 1 = BROWN
- 2 = WHITE
- 3 = BLUE
- 4 = BLACK



SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	THERMOPLASTIC PUR/BLACK
MOLDED HEAD MATERIAL/COLOR	THERMOPLASTIC PUR/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
OUTER CABLE JACKET MATERIAL/COLOR	PVC/YELLOW
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	4x18 AWG
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68



CABLE LENGTH	TOLERANCE
+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER	
STRIP LENGTH	TOLERANCE
0-7mm	±0.0mm
8-20mm	±0.0mm
20-40mm	±0.0mm
40-60mm	±0.0mm
70-100mm	±0.0mm
OVER 100mm	±0.0mm

NOTES:

1. "M" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. MATERIAL 2. SEE SPECIFICATIONS 3. FINISH 4. SEE SPECIFICATIONS	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	DATE: 07/20/00 SCALE: 1=1.0	DESCRIPTION RKC 4.4T-*--RSC 4.4T
	NO. AND ANGLE PROJECTION 	DWG: JBJ DESK:	IDENTIFICATION NO. RKC 4.4T-*--RSC 4.4T
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0.9 TO 6 ±0.1 6 TO 30 ±0.2 30 TO 200 ±0.3 OVER 200 ±0.4 ANGLES ±1° ALL INCH DIMENSIONS ARE REFERENCE ONLY		LIMIT OF MEASUREMENT <b>MILLIMETER   INCH  </b>	REV: E
MATERIAL: SEE SPECIFICATIONS FINISH: SEE SPECIFICATIONS		00 NOT SCALE THIS DRAWING	FILE: 777000641

E	UPDATE PER ECO.	JR	05/29/07	17752	ECO NO.
REV	Description	BY	DATE		