

2, 3 and 4-Wire *minifast*® Cordsets, Heavy Duty

- Straight Female Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 600 V, 9 A



Housing Style	Part Number	Cable	Features	Pinout	
	RKM 26-*M	STOW PVC Yellow 2x16 AWG 105°C 10.4 mm OD Cable #RF50561-*M [†]	<i>flexlife</i> ®	1. WH 2. BK	
	RKM 35-*M	STOW PVC Yellow 3x16 AWG 105°C 10.4 mm OD Cable #RF50537-*M [†]	<i>flexlife</i>	1. GN 2. RD/BK 3. RD/WH	
	RKM 35-*M/S600	SOOW CPE Yellow 3x16 AWG 105°C 10.3 mm OD Cable #RF50596-*M [†]	<i>Weld Flash Immune, Flame Immune</i>		
	RKM 36-*M	STOW PVC Yellow 3x16 AWG 105°C 10.4 mm OD Cable #RF50536-*M [†]	<i>flexlife</i>	1. GN 2. BK 3. WH	
	RKM 36D-*M/S1062	STOW PVC Yellow 3x16 AWG 105° C 10.4 mm OD Cable #RF50536-*M [†]	<i>flexlife</i> ® Cable, PVC plug body with PVC contact carriers	1. GN 2. BK 3. WH	

* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths.
Standard coupling nut material is nickel plated brass "RKM .."; "RK .." indicates nylon and "RKV .." indicates 316 stainless steel.
[†] See Section N for *reelfast*® cable information.