

2-Wire M12 *eurofast*® Cordsets, Standard Plug Body

- Straight Female Connector
- NEMA 1, 3, 4, 6P
- IEC IP 68 Protection
- 250 VAC/300 VDC, 4 A



Housing Style	Part Number	Cable	Features	Pinout
	RK 4.2T-*	AWM PVC Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50529- <sup>†</sup> M <sup>†</sup>	<i>flexlife</i> ®	
	RK 4.2T-*/S90	AWM PUR Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50772- <sup>†</sup> M <sup>†</sup>	<i>Cut/Abrasion Immune</i>	
	RK 4.2T-*/S748	AWM PVC Yellow 2x22 AWG 105°C 5.2 mm OD Cable #RF50650- <sup>†</sup> M <sup>†</sup>		
	RK 4.21T-*/S1511	AWM PVC Grey 2x20 AWM PVC 105°C 5.2 mm OD Cable #RF50529- <sup>†</sup> M <sup>†</sup>	<i>flexlife</i>	
	RK 4.21T-*	AWM PVC NAMUR Blue 2x20 AWG 105°C 5.2 mm OD Cable #RF20003- <sup>†</sup> M <sup>†</sup>		
	RK 4.21T-*/S90	AWM PUR NAMUR Blue 2x20 AWG 105°C 5.2 mm OD Cable #RF50657- <sup>†</sup> M <sup>†</sup>	<i>Cut/Abrasion Immune</i>	
	RK 4.22T-*	AWM PVC Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50529- <sup>†</sup> M <sup>†</sup>	<i>flexlife</i>	
	RK 4.23T-*	AWM PVC Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50529- <sup>†</sup> M <sup>†</sup>	<i>flexlife</i>	

\* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

\*\* Standard coupling nut material is nickel plated brass "RK .."; "RKK .." indicates nylon and "RKV .." indicates 316 stainless steel.

† See Section N for *reelfast*® cable information.