

2 and 3-Wire *minifast*® Cordsets, Standard

- Straight Male Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 300 V, 9 A



Housing Style	Part Number	Cable	Features	Pinout	
	RSM 20- *M	AWM PVC Yellow 2x18 AWG 105°C 7.3 mm OD Cable #RF50511-*M [†]	<i>flexlife</i> ®	1. BN 2. BU	
	RSM 30-*M	AWM PVC Yellow 3x18 AWG 105°C 7.3 mm OD Cable #RF50512-*M [†]	<i>flexlife</i>		
	RSM 30-*M/S90	AWM PUR Yellow 3x18 AWG 105°C 7.3 mm OD Cable #RF50545-*M [†]	<i>Cut Abrasion Immune</i>	1. GN/YE 2. BN 3. BU	
	RSM 30-*M/S101	AWM TPE Yellow 3x18 AWG 105°C 7.2 mm OD Cable #RF51173-*M [†]	<i>flexlife-10, high flex over 10 million cycles</i>		
	RSM 311-*M	AWM PVC Yellow 3x18 AWG 105°C 7.3 mm OD Cable #RF50520-*M [†]	<i>flexlife</i>	1. GN 2. RD/BK 3. RD/WH	
	RSM 311-*M/S600	SJOOW CPE, Yellow 3x18 AWG 105°C 8.0 mm OD Cable #RF50658-*M [†]	<i>Weld Flash Immune, Flame Immune</i>		
	RSM 311-*M/XOR/S620	AWM Irradiated PVC Yellow, 3x18 AWG 80°C 5.7 mm OD Cable #RF04159-*M [†]	<i>Weld Resistance</i>	1. GN 2. RD 3. RD/WH	
	RSM 31-*M	AWM PVC Yellow 3x18 AWG 105°C 7.3 mm OD Cable #RF50513-*M [†]	<i>flexlife</i>		
	RSM 31-*M/S600	SJOOW CPE Yellow 3x18 AWG 105°C 8.0 mm OD Cable #RF50654-*M [†]	<i>Weld Flash Immune, Flame Immune</i>	1. BK 2. BN 3. BU	
	RSM 31-*M/S759	AWM PVC Grey 3x22 AWG 80°C 5.2 mm OD Cable #RF04106-*M [†]	<i>Braided Shield</i>		

* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths.
Standard coupling nut material is nickel plated brass "RSM .."; "RS .." indicates nylon and "RSV .." indicates 316 stainless steel.
[†] See Section N for *reelfast*® cable information.