

### 3M™ Heat Shrink Heavy-Wall Cable Sleeves ITCSN (continued)

| Order No.                        | UPC          | Cable Size            | Length         | Expanded/Recovered I.D.       | UL Spec. | Adhesive Included | Direct Bury | Case Qty.       |
|----------------------------------|--------------|-----------------------|----------------|-------------------------------|----------|-------------------|-------------|-----------------|
| ITCSN-0800-48"-Red-20 Pcs        | 051128-55500 | 8-1/0 AWG             | 48" (1,22 m)   | 0.80"/0.20"<br>(20,3/5,1 mm)  | N/A      | Yes               | No          | 20              |
| ITCSN-0800-25'-Black-Reel        | 054007-08888 | 8-1/0 AWG             | 25' (7,62 m)   | 0.80"/0.20"<br>(20,3/5,1 mm)  | N/A      | No                | No          | 1               |
| ITCSN-1100-6"-Black-25 Pcs       | 054007-08894 | 2-4/0 AWG             | 6" (152,4 mm)  | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 25              |
| ITCSN-1100-6"-Black-100 Pcs      | 054007-08969 | 2-4/0 AWG             | 6" (152,4 mm)  | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 100             |
| ITCSN-1100-9"-Black-25 Pcs       | 054007-08893 | 2-4/0 AWG             | 9" (228,6 mm)  | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 25              |
| ITCSN-1100-9"-Black-100 Pcs      | 054007-08970 | 2-4/0 AWG             | 9" (228,6 mm)  | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 100             |
| ITCSN-1100-9"-Black-12-3 Pc Pks  | 051128-60079 | 2-4/0 AWG             | 9" (228,6 mm)  | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 3/pk,<br>12 pks |
| ITCSN-1100-9"-Red-12-3 Pc Pks    | 051128-60080 | 2-4/0 AWG             | 9" (228,6 mm)  | 1.10"/0.37"<br>(27,9/9,4 mm)  | N/A      | Yes               | No          | 3/pk,<br>12 pks |
| ITCSN-1100-12"-Black-10 Pcs      | 054007-08892 | 2-4/0 AWG             | 12" (304,8 mm) | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 10              |
| ITCSN-1100-12"-Black-100 Pcs     | 054007-08971 | 2-4/0 AWG             | 12" (304,8 mm) | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 100             |
| ITCSN-1100-48"-Black-5 Pcs       | 054007-08904 | 2-4/0 AWG             | 48" (1,22 m)   | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 5               |
| ITCSN-1100-48"-Black-20 Pcs      | 054007-08972 | 2-4/0 AWG             | 48" (1,22 m)   | 1.10"/0.37"<br>(27,9/9,4 mm)  | UL 486D  | Yes               | Yes         | 20              |
| ITCSN-1100-25'-Black-Reel        | 054007-08891 | 2-4/0 AWG             | 25' (7,62 m)   | 1.10"/0.37"<br>(27,9/9,4 mm)  | N/A      | No                | No          | 1               |
| ITCSN-1500-9"-Black-10 Pcs       | 054007-08897 | 3/0 AWG-<br>400 kcmil | 9" (228,6 mm)  | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 10              |
| ITCSN-1500-9"-Black-50 Pcs       | 054007-08973 | 3/0 AWG-<br>400 kcmil | 9" (228,6 mm)  | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 50              |
| ITCSN-1500-9"-Black-12-3 Pc Pks  | 051128-60081 | 3/0 AWG-<br>450 kcmil | 9" (228,6 mm)  | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 3/pk,<br>12 pks |
| ITCSN-1500-12"-Black-10 Pcs      | 054007-08896 | 3/0 AWG-<br>400 kcmil | 12" (304,8 mm) | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 10              |
| ITCSN-1500-12"-Black-50 Pcs      | 054007-08974 | 3/0 AWG-<br>400 kcmil | 12" (304,8 mm) | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 50              |
| ITCSN-1500-48"-Black-5 Pcs       | 054007-08905 | 3/0 AWG-<br>400 kcmil | 48" (1,22 m)   | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 5               |
| ITCSN-1500-48"-Black-20 Pcs      | 054007-08975 | 3/0 AWG-<br>400 kcmil | 48" (1,22 m)   | 1.50"/0.50"<br>(38,1/12,7 mm) | UL 486D  | Yes               | Yes         | 20              |
| ITCSN-1500-25'-Black-Reel        | 054007-08895 | 3/0 AWG-<br>450 kcmil | 25' (7,62 m)   | 1.50"/0.50"<br>(38,1/12,7 mm) | N/A      | No                | No          | 1               |
| ITCSN-2000-9"-Black-10 Pcs       | 054007-08900 | 250-750 kcmil         | 9" (228,6 mm)  | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 10              |
| ITCSN-2000-9"-Black-50 Pcs       | 054007-08976 | 250-750 kcmil         | 9" (228,6 mm)  | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 50              |
| ITCSN-2000-12"-Black-10 Pcs      | 054007-08899 | 250-750 kcmil         | 12" (304,8 mm) | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 10              |
| ITCSN-2000-12"-Black-50 Pcs      | 054007-08977 | 250-750 kcmil         | 12" (304,8 mm) | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 50              |
| ITCSN-2000-12"-Black-12-3 Pc Pks | 051128-60082 | 250-750 kcmil         | 12" (304,8 mm) | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 3/pk,<br>12 pks |
| ITCSN-2000-48"-Black-5 Pcs       | 054007-08906 | 250-750 kcmil         | 48" (1,22 m)   | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 5               |
| ITCSN-2000-48"-Black-20 Pcs      | 054007-08978 | 250-750 kcmil         | 48" (1,22 m)   | 2.00"/0.65"<br>(50,8/16,5 mm) | UL 486D  | Yes               | Yes         | 20              |