


3MTM Economy Vinyl Electrical Tape 1400

Description 3MTM Economy Vinyl Electrical Tape 1400 is a black 7 mil thick, general use vinyl-insulating tape. It is designed to perform continuously in temperatures up to 80°C (176°F). This tape has a polyvinyl chloride (PVC) backing with pressure-sensitive rubber based adhesive. It inhibits corrosion of electrical conductors.

Agency Approvals & Self Certifications UL Listed; UL 510 Standard
 “Insulating Tape” product category OANZ, File # 129200

RoHS 2002/95/EC 

RoHS Compliant 2002/95/EC* means that the product or part (“Product”) does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2002/618/EC, unless the substance is in an application that is exempt under RoHS. This information represents 3M’s knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

Applications

- Electrical insulation for all wire and cable splices rated up to 600 volts and 80°C (176°F).
- Harnessing of wires and cables

Installation Techniques The tape shall be applied in half-lapped layers with sufficient tension to produce a uniform wind. Apply the tape with no tension on the last wrap to prevent flagging.

Typical Properties Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (~23°C) unless otherwise stated.

Physical	Property (Test Method)	Typical Value
		US units (metric)
	Color	Black
	Adhesive	Pressure-sensitive rubber based
	Type of Backing	Polyvinyl chloride
	Thickness (UL 510)	7 mils
	Adhesion to Backing (ASTM D1000)	16 oz/in
	Adhesion to Steel (ASTM D1000)	16 oz/in
	Breaking Strength (ASTM D1000)	14 lbs/in
	Ultimate Elongation (ASTM D1000)	150%
	Dielectric Strength (ASTM D1000)	Standard Condition 1000 V/mil High Humidity 90% of std.
	Flammability (UL 510)	Pass
	Voltage Raging (UL 510)	600V
	Flagging (ASTM D1000)	<0.25 inch



3M™ Economy Vinyl Electrical Tape 1400

Shelf Life & Storage This product has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).

Availability Please contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1-800-245-3573.

Important Notice All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

3M is a trademark of 3M Company.



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800 245 3563
FAX: 800 245 0329
www.3M.com/electrical

Please recycle
© 3M 2010 All rights reserved
78-8127-9822-7 A