

3M™ Tekk Protection™ Readers Safety Glasses 91191-00002T, +1.5 Bk Frm Clr Lens

UPC# 10078371611108 CAT# 91191-00002T 3M ID 70005130235



Classic dual lens design provides 99.9% UV protection with a built in bifocal power of +1.5. Black frame with clear lens. Adjustable temple lengths and lightweight construction. Meets ANSI Z87.1-2003, CSA Z94.3 -2005 standards

- Reader lenses available (+1.5)
- Adjustable temple lengths
- Meets the requirements of ANSI Z87.1-2003 and CSA Z94.3-2007

Specifications

ANSI Requirements	ANSI Z87.1-2003 and CSA Z94.3-2007
Color	Black
Features	Soft Temples, Adjustable Temples
Frame Color	Black
Lens Coating	Anti-Fog
Lens Color	Clear
Lens Type	Non-Mirrored
Protection Type	Glasses