



Actual

Catalog Number: 10-407
Product ID: 7TAA008610R0002
UPC Number: 78378600475
EAN Number: 05415022189636
Status: Active

High temperature Porcelain Wire Connector HI-7.

- Three sizes accommodate #18-14AWG stranded Copper
- 300 Volt rated.
- For high temperature applications over 105 degree C

North American Specifications (UNSPSC)

UNSPSC	39121445 Twist on wire connector
IGCC	4665 Twist on wire connector
Brand Name	T&B
Type	Wire Connectors & Termination
Special Features	Three sizes accommodate #18-14AWG stranded Copper
Application	For high temperature applications over 105 degree C
Standard	UL E9809, CSA 6591
Conductor Range	# 18-12 AWG
Material	Porcelain
Color	White
Voltage Rating	300V
Temperature Rating	Higher than 105 Degrees Celsius (221 F)

Packaging

Outer Quantity	100
Weight Uom	0.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com