



Technical details

Material Body	Polyamide 6
Seal	Neoprene
Colour	Black
Protection Class	IP 68, 5 bar
Temperature Range	-30°C to 80°C permanent
Operational temperature	Up to +150°C intermittent
Approvals	UL, CSA & VDE
Manufactured according to the requirements of EN 50262	

NPT Thread - Standard Series Polyamide Cable Glands

Black	NPT3/8	NPT3/8	NPT1/2	NPT1/2	NPT1/2	NPT1/2	NPT3/4	NPT3/4	NPT1	NPT1/4
TL (Inch)	0.590	0.590	0.590	0.590	0.590	0.590	0.590	0.590	0.709	0.590
Spanner (Inch)	0.866	0.945	0.945	0.866	1.063	1.299	1.063	1.299	1.654	1.811
Clamping Range (Inch)										
Min Ø	0.197	0.236	0.236	0.197	0.394	0.511	0.394	0.511	0.709	0.709
Max Ø	0.394	0.472	0.472	0.394	0.551	0.709	0.551	0.709	0.984	0.984