



Actual

**Catalog Number:** AMTT20  
**Product ID:** 7TAH006400R0219  
**UPC Number:** 78378625921  
**EAN Number:** 05415022245547  
**Status:** Active

AMT Splice Offset, 2-Port, PVC Insulated, Wire Range 2/0-14 Str, Length 1.63 Inches, Width 1.68 Inches, Height 1.62 Inches, Hex Size 3/16 Inches

- PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
- Compact design provides space efficiencies.
- All cable entry are equipped with an anti-oxidation compound.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	AMT Connector
Special Features	PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
Standard	UL E9809, CSA 6591
Material	Aluminum
Color	Black
Insulation	PVC
Number Of Ports	2

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	5x5.2x4
Weight Uom	1 lbs. per 100

### Documents / Support Tools

SDS US 1	sds-00041-tb2
Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Marketing Brochure US 1	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)