



Representative

Catalog Number: ASP1
Product ID: 7TAH007890R1131
UPC Number: 78378661060
Status: Active

Type ASP Aluminum Splice, Max 35KV, Wire Size 1 Str, Length 2-3/8 Inch, Tin Plated, Die Color Code Gold

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Aluminum Splice
Special Features	Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Conductor Range	1 Str
Material	Aluminum
Finish	Tin Plated
Color	Gold
Voltage Rating	35KV

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Useful for stranded conductors	Y
Material	Other
Surface protection	Tinned
Insulation	None
Voltage row	Up to 35kV

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	100
Outer Dimensions (inches)	12.5x6.75x4.25
Weight Uom	4 lbs. per 100

Documents / Support Tools

SDS US 1	sds-00012-tb2
Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com