



Representative

Catalog Number: PAE4141-9
Product ID: 7TAA267200R0051
UPC Number: 78378633031
EAN Number: 05415022349139
Status: Active

Aluminum Type PAE - Parallel Groove Clamp, Extruded Type for Wire Range Main: 4/0 AC-SR-2 Solid 4-6 AR Tap: 4/0 ACSR-2 Solid, 4-6 AR

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Parallel-Groove Clamp
Special Features	Galvanized Steel Hardware Provides High Strength for Heavy-Duty Applications. Install with Live Line Tools you Already Have. Dual-Rated for Aluminum-to-Copper Connections.
Application	Securing Conductors
Standard	RUS Listed
Size	Height 2 X Length 1-3/8 X Width 2 inch, Bolt 3/8 inch
Connection	Bolted
Conductor Range	Main: 4/0 ACSR-2 Solid 4-6 AR Tap: 4/0 ACSR-2 Solid, 4-6 AR
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	25
Inner Dimensions (inches)	8.125x7.25x6.375
Outer Quantity	100
Outer Dimensions (inches)	17.1x13.6x8
Weight Uom	23.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com