

**UL 1077****T&B Catalog Number:**

S203P-Z25

UPC Number:

66201917217

Status:

Active

Description:

MCB 3P Z 25A 480Y/277 SUPP

Features

High performance MCB provides compact supplementary, energy limiting, circuit protection

Fast breaking time

Bus connection system

Finger safe terminals

Suitable for reverse feed

Application

For use as a supplemental protection device

Designed for allowing higher in-rush currents during system startup such as motors and transformers

For use with inductive loads

General

Mounting Method DIN Rail

Trip Type Thermal-magnetic

Number of Poles 3

Series S200P-Z

Terminal Type Screw

Approvals

UL Class UL 1077

Dimension Information

H x W x D (inches) 3.35 x 2.07 x 2.98

H x W x D (mm) 88 x 52.5 x 69

Specifications

Rated Current (Amps) 25

Rated Voltage AC 480Y/277

Interrupt Rating (kA) 10

Trip Curve Z

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 94.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com