



Representative

Catalog Number: 1SVR405611R1000
UPC Number: 66201921388
Status: Active

Plugin control relay with 24 VDC rated control supply voltage, SPDT (2 c/o) contacts, contacts, without LED indicator and 250 V, 12 A contact rating

North American Specifications (UNSPSC)

UNSPSC	39122326 Socket relay
IGCC	5360 Socket relay
Brand Name	ABB
Type	General purpose relay
Special Features	This relay operates with a 24 V DC rated control supply voltage and has a 2 c/o (SPDT) output with contacts rated at 250 V / 12 A. The relay has an integrated blue test button for manual actuation and locking of the output contacts. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories.
Application	For applications where low current control voltage is used to switch higher current or voltage loads
Standard	RoHs, CSA, CE, GOST
Size	21.2x35.6x27.5mm

Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	7.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com