

NF 4-pole contactor relays

Main accessories



CA4-10



CA4-22N



CAL4-11



TEF4-ON



LDC4



BX4



BX4-CA

Ordering details (1)

| For contactor relays | Auxiliary contacts | Type | Order code | Pkg qty | Weight (1 pce) |
|----------------------|--------------------|------|------------|---------|----------------|
| | | | | | kg |

Front-mounted instantaneous auxiliary contact blocks

| 4-pole NF | NO | NC | Type | Order code | Pkg qty | Weight (1 pce) |
|-----------|----|----|----------|-----------------|---------|----------------|
| | 1 | 0 | CA4-10 | 1SBN010110R1010 | 1 | 0.014 |
| | 1 | 0 | CA4-10-T | 1SBN010110T1010 | 10 | 0.014 |
| | 0 | 1 | CA4-01 | 1SBN010110R1001 | 1 | 0.014 |
| | 0 | 1 | CA4-01-T | 1SBN010110T1001 | 10 | 0.014 |
| | 4 | 0 | CA4-40N | 1SBN010140R1240 | 1 | 0.055 |
| | 3 | 1 | CA4-31N | 1SBN010140R1231 | 1 | 0.055 |
| | 2 | 2 | CA4-22N | 1SBN010140R1222 | 1 | 0.055 |
| | 1 | 3 | CA4-13N | 1SBN010140R1213 | 1 | 0.055 |
| NF..40E | 0 | 4 | CA4-04N | 1SBN010140R1204 | 1 | 0.055 |

Front-mounted auxiliary contact blocks with N.O. leading contact and N.C. lagging contact

| 4-pole NF | NO | NC | Type | Order code | Pkg qty | Weight (1 pce) |
|-----------|----|----|--------|-----------------|---------|----------------|
| | - | - | CC4-10 | 1SBN010111R1010 | 1 | 0.014 |
| | - | 0 | CC4-01 | 1SBN010111R1001 | 1 | 0.014 |

Side-mounted instantaneous auxiliary contact blocks

| NF | NO | NC | Type | Order code | Pkg qty | Weight (1 pce) |
|----|----|----|-----------|-----------------|---------|----------------|
| | 1 | 1 | CAL4-11 | 1SBN010120R1011 | 1 | 0.040 |
| | 1 | 1 | CAL4-11-T | 1SBN010120T1011 | 10 | 0.040 |

| For contactors | Time delay range selected by switch | Delay type | Auxiliary contacts | Type | Order code | Pkg qty | Weight (1 pce) |
|----------------|-------------------------------------|------------|--------------------|------|------------|---------|----------------|
| | | | | | | | kg |

Electronic timers

| NF | Time delay range | Delay type | NO | NC | Type | Order code | Pkg qty | Weight (1 pce) |
|----|------------------|------------|----|----|----------|-----------------|---------|----------------|
| | 0.1...1 s | ON-delay | 1 | 1 | TEF4-ON | 1SBN020112R1000 | 1 | 0.065 |
| | 1...10 s | OFF-delay | 1 | 1 | TEF4-OFF | 1SBN020114R1000 | 1 | 0.065 |
| | 10...100 s | | | | | | | |

Note: Rated control circuit voltage U_c 24...240 V 50/60 Hz or DC.

Additional coil terminal block

| NF | Type | Order code | Pkg qty | Weight (1 pce) |
|----|------|-----------------|---------|----------------|
| | LDC4 | 1SBN070156T1000 | 10 | 0.010 |

Protective covers

| All 1-stack contactor relays | Type | Order code | Pkg qty | Weight (1 pce) |
|---|--------|-----------------|---------|----------------|
| | BX4 | 1SBN110108T1000 | 10 | 0.006 |
| 4-pole CA4 auxiliary contact blocks and TEF4 electronic timer | BX4-CA | 1SBN110109W1000 | 50 | 0.001 |

(1) For more information, refer to main catalog "Accessories" section.