

Products Low Voltage Products and Systems Control Products Pilot Devices Pilot Devices Accessories

### General Information

<b>Extended Product Type:</b>	MLBL-04G
<b>Product ID:</b>	1SFA611621R1042
<b>EAN:</b>	7320500372968
<b>Catalog Description:</b>	MLBL-04G LED block
<b>Long Description:</b>	Modular LED block - 110-130 V AC, integrated LED - Green - Illuminated

### Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Accessory Type:</b>	LED and lamp blocks
<b>Color:</b>	Green
<b>Country of Origin:</b>	China (CN)
<b>Customs Tariff Number:</b>	85369001
<b>Data Sheet, Technical Information:</b>	1SFC151003C0201
<b>Declaration of Conformity - CE:</b>	1SFA1-83
<b>E-nummer:</b>	3705060
<b>EAN:</b>	7320500372968
<b>ETIM 4:</b>	EC002024 - Accessories for control circuit devices
<b>ETIM 5:</b>	EC000204 - Lamp holder block for control circuit devices
<b>ETIM 6:</b>	EC000204 - Lamp holder block for control circuit devices
<b>Environmental Information:</b>	1SFC151010D0201
<b>Illumination:</b>	Illuminated
<b>Instructions and Manuals:</b>	1SFC151003C0201
<b>Invoice Description:</b>	LAMP BLOCK#MLBL-04G
<b>Lamp Type:</b>	110-13 V AC, integrated LED
<b>Luminance:</b>	1200 millicandela
<b>Minimum Order Quantity:</b>	10 piece
<b>Object Classification Code:</b>	E
<b>Package Level 1 Gross Weight:</b>	0.01 kg
<b>Package Level 1 Height:</b>	0.01 m
<b>Package Level 1 Length:</b>	0.15 m
<b>Package Level 1 Width:</b>	0.11 m
<b>Product Main Type:</b>	MLBL
<b>Product Name:</b>	LED block
<b>Product Net Depth:</b>	0.035 m
<b>Product Net Height:</b>	0.010 m
<b>Product Net Weight:</b>	0.01 kg
<b>Product Net Width:</b>	0.044 m
<b>Product Range:</b>	Modular range
<b>Product Type:</b>	MLBL
<b>Rated Current (I<sub>n</sub>):</b>	8.5 mA
<b>Rated Operational Voltage:</b>	110-130 V AC
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Green Modular LED block
<b>Suitable For:</b>	MP1 MP2

MP3  
MP4  
MPD1  
MPD2  
MPD3  
MPD4  
MPD5  
MPD11  
MPD12  
MPD13  
MPD14  
MPD15  
MPD16  
MPM1  
MPM2  
KP6  
MPET3  
MPEP3  
MPEK3  
MPET4  
MPEP4  
MPEK4  
MPMT3  
MPMT4  
MPMP3  
MPMP4  
M2SS1  
M2SS2  
M2SS3  
M2SS4  
M2SS5  
M2SS6  
M3SS1  
M3SS2  
M3SS3  
M3SS4  
M3SS5  
M3SS6  
M3SS7  
M3SS8  
M3SSC1  
M3SSC2  
M3SSC3  
M3SSC4  
M3SSC5  
M3SSC6  
M3SSC7  
M3SSC8  
M2SSK1  
M2SSK2  
M2SSK3  
M3SSK1  
M3SSK2  
M3SSK3  
MTS1  
MTS2  
MTS3  
MJS1  
MJS2  
MJS5  
MJS6  
MJS7  
MJS8  
MJS11  
MJS12

---

UNSPSC: 39120000

Wave Length: 520 nm

---