

**Catalog Number:** XT4NU3250AFF000XXX  
**UPC Number:** 88861440758  
**Status:** Active

Tmax Breaker Frame Size XT4N 250 Thermal Magnetic Fixed 250-2500 Three-Pole Fixed + Front Flat Terminals Underwriters Laboratory/Canadian Standards Association

**North American Specifications (UNSPSC)**

UNSPSC	39121616 Molded case circuit breakers
IGCC	4927 Molded case circuit breakers
Brand Name	ABB
Sub Brand	Tmax XT
Type	Molded case circuit breaker
Special Features	Feature high specific let-through current peak and energy limiting characteristics that allow the circuits and equipment on the load side to be sized in Optimum way.
Application	Ideal solution for all distribution levels from the main low voltage switchboard to the subswitchboards in the installation
Standard	UL 80% rated / IEC dual rated
Frame	XT4 - to 250A, 600V (UL) / 250A, 690V (IEC) - Thermal magnetic and Electronic protection
Trip Type	Thermal magnetic fixed (TMF)
Number Of Poles	3 Poles

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	6.61x5.71x8.27
Weight Uom	5.33 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com