



Red, White and Blue Extension Cord

This rugged Red, White and Blue Contractor Grade Extension Cord is dedicated to the American Contractor. Made in the USA by an American company. Coleman Cable's vinyl Pro-Power outdoor extension cords all have molded water resistant connectors with reinforced blades that make them suitable for all weather outdoor use. The lighted female ends let you know that there is power ready and available. The new color scheme lets you know that they are a Coleman Cable American original.

Features & Benefits

- UL listed
- OSHA and NEC compliant
- Lighted female ends let you know there is power
- Molded male and female ends-water resistant
- ProPower 12 gauge construction-the standard of the construction industry
- Highly visible red cord, with two extruded white stripes
- Blue stenciled stripe with "MADE IN THE USA by CCI****PROUD TO BE AMERICAN"
- Displays America's colors on the jobsite



Part Number	Wire Ga/Cond	Wire Type	Color / Ends	Length in ft	Legend	125 V Rating	Pack Qty
02548-USA1	12/3	SJTW	Red/White/Blue Clear Lighted Female End	50	MADE IN THE USA BY CCI ****PROUD TO BE AMERICAN	15A	6
02549-USA1	12/3	SJTW	Red/White/Blue Clear Lighted Female End	100	MADE IN THE USA BY CCI ****PROUD TO BE AMERICAN	15A	4

Application Information

- Residential and commercial construction
- Heavy-duty industrial applications
- Any time a highly visible cord is required

Product Construction

- 12/3 SJTW in both 50 and 100 ft. lengths
- Flexible from -40° C to 75° C
- 15 AMP 125 VAC

Industry Approvals

- UL Listed
- OSHA
- NEC

Proud
Supporter of



**WOUNDED WARRIOR
PROJECT®**

