



T1035

This easy-to-install switch handles all types of lighting, and features sunrise/sunset activation



MODEL & RATINGS

T1035	2400 W max.	1 HP @ 120 V	20 A
--------------	-------------	--------------	------

SPECIFICATIONS

PROGRAMMING

Sunrise/sunset
2 optional settings (1 on, 1 off)

OPERATING MODES

Manual (conventional on/off switch)
Automatic

CONNECTION

3 wire (line, load, neutral)

DIMENSIONS (H•W•D)

68 x 43 x 40 mm / 2.7 x 1.8 x 1.6 in.

FEATURES

Sleek design mounts flush with wall

Works with motors and all types of lighting
(compatible with electronic ballasts, compact fluorescent lights and tungsten lights up to 5 A)

LCD shows time, day and load status

Installs in standard decorative wall plate (not included)

Manual override turns load on / off without affecting programming

3-wire installation (requires line & neutral wires)

Built-in rechargeable battery

Memory protected during power outages

ADDITIONAL INFORMATION

SUNRISE/SUNSET PROGRAMMING

- No need to continually re-program on / off times – ideal for lighting
- Calculates on (sunset) and off (sunrise) times according to the longitude and latitude entered for your city (coordinates are provided in the instruction manual)
- On/off optional settings can be used, for example, to turn lights off at midnight and on again before sunrise
- Simple daylight savings time adjustment