

# HOLOPHANE®

ROUND CAPACITOR						
Lamp	Catalog Number	Input Voltage	Ballast A x B x C	Round Capacitor A x B	Ballast Type	Net Wt. kg (lbs)
35W HPS	<b>RBK035HP12B</b>	120	2.50 x 3.00 x 2.30	1.75 x 3.57	R- Reactor	2 (4)
50W HPS	<b>RBK050HP12B</b>	120	2.50 x 3.00 x 2.31	1.75 x 3.57	R- Reactor	2 (5)
	<b>RBK050HP48B</b>	480	4.00 x 2.87 x 3.00	1.75 x 3.57	HX - High Reactance	2 (5)
	<b>RBK050HPMTB</b>	120/208/240/277	4.00 x 2.87 x 2.69	1.75 x 3.57	HX - High Reactance - Multi-Tap	2 (5)
70W HPS	<b>RBK070HP12B</b>	120	2.50 x 3.00 x 2.36	1.75 x 3.94	R- Reactor	3 (6)
	<b>RBK070HP48B</b>	480	4.00 x 2.87 x 3.00	1.75 x 2.94	HX - High Reactance	3 (6)
	<b>RBK070HPMTB</b>	120/208/240/277	4.00 x 2.87 x 2.68	1.75 x 2.94	HPF Auto Multi-Tap	3 (6)
100W HPS	<b>RBK100HP12B</b>	120	2.50 x 3.00 x 2.59	1.75 x 3.94	R- Reactor	4 (8)
	<b>RBK100HP48B</b>	480	4.00 x 2.87 x 3.81	1.75 x 2.94	HX - High Reactance	4 (8)
	<b>RBK100HPMTB</b>	120/208/240/277	4.00 x 2.87 x 3.25	1.75 x 2.94	HPF Auto Multi-Tap	4 (8)
150W HPS 55V	<b>RBK15AHP12B</b>	120	2.50 x 3.00 x 3.30	1.75 x 4.81	R- Reactor	5 (10)
	<b>RBK15AHP48B</b>	480	4.00 x 2.87 x 4.10	1.75 x 2.94	HX - High Reactance	5 (10)
	<b>RBK15AHPMTB</b>	120/208/240/277	4.00 x 2.87 x 3.75	1.75 x 2.94	HPF Auto Multi-Tap	5 (10)
150W HPS 100V	<b>RBK15BHP48B</b>	480	4.00 x 2.87 x 3.81	1.75 x 2.94	HX - High Reactance	4 (9)
	<b>RBK15BHPMTB</b>	120/208/240/277	4.00 x 2.87 x 3.38	1.75 x 2.94	HPF Auto Multi-Tap	4 (9)
200W HPS	<b>RBK200HP48B</b>	480	4.87 x 4.25 x 3.13	1.75 x 4.81	CWA	5 (12)
	<b>RBK200HPMTB</b>	120/208/240/277	4.87 x 4.25 x 3.13	1.75 x 4.81	CWA - Multi-Tap	5 (12)
250W HPS	<b>RBK250HP48B</b>	480	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA	5 (12)
	<b>RBK250HPMTB</b>	120/208/240/277	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA - Multi-Tap	5 (12)
	<b>RBK25LHP48B</b>	480	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA (Energy Saving)	5 (12)
	<b>RBK25LHPMTB</b>	120/208/240/277	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA - Multi-Tap (Energy Saving)	5 (12)
	<b>RBK25RHPXXB<sup>1</sup></b>	See note 1	4.87 x 4.25 x 4.63	1.75 x 3.94	Mag-Reg	7 (16)
400W HPS	<b>RBK400HP48B</b>	480	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA	8 (17)
	<b>RBK400HPMTB</b>	120/208/240/277	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA - Multi-Tap	8 (17)
	<b>RBK40LHP48B</b>	480	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA (Energy Saving)	8 (18)
	<b>RBK40LHPMTB</b>	120/208/240/277	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA - Multi-Tap (Energy Saving)	8 (18)
	<b>RBK40RHPXXB<sup>1</sup></b>	See note 1	6.12 x 4.25 x 4.69	2.50 x 3.37	Mag-Reg	10 (22)
	<b>RBK400HP48C</b>	480	4.87 x 4.25 x 4.31	2.50 x 3.37	CWA	8 (17)
1000W HPS	<b>RBK400HPMTC</b>	120/208/240/277	4.87 x 4.25 x 4.31	2.50 x 3.37	CWA - Multi-Tap	8 (17)
	<b>RBKC10HP48B</b>	480	6.12 x 4.25 x 5.94	2.50 x 3.87	CWA	13 (28)
	<b>RBKC10HPMTB</b>	120/208/240/277	6.12 x 4.25 x 5.94	2.50 x 3.87	CWA - Multi-Tap	13 (28)
50W MH	<b>RBK050MHMTB</b>	120/208/240/277	3.94 x 2.81 x 2.91	1.75 x 2.94	CWA - Multi-Tap	3 (6)
70W MH	<b>RBK070MHMTB</b>	120/208/240/277	3.94 x 2.81 x 2.80	1.75 x 2.94	CWA - Multi-Tap	3 (7)
100W MH	<b>RBK100MHMTB</b>	120/208/240/277	3.94 x 2.81 x 2.90	1.75 x 2.94	CWA - Multi-Tap	4 (9)
150W MH	<b>RBK150MHMTB</b>	120/208/240/277	3.94 x 2.81 x 3.91	1.75 x 2.94	CWA - Multi-Tap	5 (10)
175W MH	<b>RBK175MH48B</b>	480	4.00 x 2.87 x 3.82	1.75 x 2.94	CWA	5 (10)
	<b>RBK175MHMTB</b>	120/208/240/277	4.00 x 2.87 x 3.68	1.75 x 2.94	CWA - Multi-Tap	5 (10)
	<b>RBK175PM48B</b>	480	4.00 x 2.87 x 3.82	1.75 x 2.94	CWA	5 (10)
	<b>RBK175PMMTB</b>	120/208/240/277	4.00 x 2.87 x 3.68	1.75 x 2.94	CWA - Multi-Tap	5 (10)
250W MH	<b>RBK250MH48B</b>	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA	5 (11)
	<b>RBK250MHMTB</b>	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap	5 (11)
	<b>RBK25LMH48B</b>	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA (Energy Saving)	7 (15)
	<b>RBK25LMHMTB</b>	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap (Energy Saving)	7 (15)
	<b>RBK250PM48B</b>	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA	5 (11)
	<b>RBK250PMMTB</b>	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap	5 (11)
	<b>RBK25LPM48B</b>	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA (Energy Saving)	7 (15)
<b>RBK25LPMMTB</b>	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap (Energy Saving)	7 (15)	
320W MH	<b>RBK320PM48B</b>	480	4.87 x 4.25 x 4.25	1.75 x 3.94	CWA	6 (14)
	<b>RBK320PMMTB</b>	120/208/240/277	4.87 x 4.25 x 4.13	1.75 x 3.94	CWA - Multi-Tap	6 (14)
350W MH	<b>RBK350PM48B</b>	480	4.87 x 4.25 x 4.00	1.75 x 4.25	R- Reactor	6 (14)
	<b>RBK350PMMTB</b>	120/208/240/277	4.87 x 4.25 x 3.66	1.75 x 4.25	R- Reactor - Multi-Tap	6 (14)
	<b>RBK35LPM48B</b>	480	4.87 x 4.25 x 4.00	1.75 x 4.25	CWA	6 (14)
	<b>RBK35LPMMTB</b>	120/208/240/277	4.87 x 4.25 x 3.66	1.75 x 4.25	CWA - Multi-Tap	6 (14)
400W MH	<b>RBK400MH48B</b>	480	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA	7 (15)
	<b>RBK400MHMTB</b>	120/208/240/277	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA - Multi-Tap	7 (15)
	<b>RBK40LMH48B</b>	480	4.87 x 4.25 x 4.18	1.75 x 4.81	CWA (Energy Saving)	7 (15)
	<b>RBK40LMHMTB</b>	120/208/240/277	4.87 x 4.25 x 3.88	1.75 x 4.81	CWA - Multi-Tap (Energy Saving)	7 (15)
	<b>RBK40RMHXXB<sup>1</sup></b>	See note 1	6.12 x 4.25 x 5.88	2.50 x 3.37	Mag Reg	11 (24)
	<b>RBK400PM48B</b>	480	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA	7 (15)
	<b>RBK400PMMTB</b>	120/208/240/277	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA - Multi-Tap	7 (15)
	<b>RBK40LPM48B</b>	480	4.87 x 4.25 x 4.18	1.75 x 4.81	CWA (Energy Saving)	7 (15)
	<b>RBK40LPMMTB</b>	120/208/240/277	4.87 x 4.25 x 3.88	1.75 x 4.81	CWA - Multi-Tap (Energy Saving)	7 (15)
	<b>RBK400MH48C</b>	480	4.87 x 4.25 x 4.25	2.50 x 3.37	CWA	7 (15)
	<b>RBK400MHMTC</b>	120/208/240/277	4.87 x 4.25 x 4.25	2.50 x 3.37	CWA - Multi-Tap	7 (15)
750W MH	<b>RBK750PM48C</b>	480	6.125 x 4.25 x 5.12	2.50 x 3.37	CWA	11 (24)
	<b>RBK750PMMTC</b>	120/208/240/277	6.125 x 4.25 x 5.12	2.50 x 3.37	CWA - Multi-Tap	11 (24)
1000W	<b>RBKC10MH48B</b>	480	6.12 x 4.25 x 5.12	2.50 x 3.37	CWA	11 (24)
	<b>RBKC10MH48C</b>	480	6.12 x 4.25 x 5.12	2.50 x 3.37	CWA	11 (24)
	<b>RBKC10MHMTC</b>	120/208/240/277	6.12 x 4.25 x 5.12	2.50 x 3.37	CWA - Multi-Tap	11 (24)
1500W MH	<b>RBKC15MHXXB<sup>1</sup></b>	See note 1	6.12 x 4.25 x 4.50	2.50 x 4.44	CWA	15 (32)

NOTES: 1 Insert voltage 12-120V; 20-208V; 24-240V; 27-277V; or 48-480V for "XX" in catalog number  
These voltages available at the same price