

**Intended Use**

Suitable for architectural applications where aesthetics and superior performance are required.

**Construction**

Injection-molded acrylic panels, ultrasonically welded to eliminate visible hardware.

Depth of molded letters increases toward bottom of

panel for better, more uniform illumination. Chevron directional indicators.

Long-life LEDs feature very low energy consumption and rated life up to 25 years.

Emergency operation exits use maintenance-free nickel-cadmium battery.

Recessed mounting. Rough-in section recessed into wall

or ceiling for top, back or end mounting capability.

Surface top-mount (TM) option available on non-emergency exits, and attaches directly to J-box. Can be used for pendant mounting.

Special wording available; consult factory.

**Listings**

UL Listed. Meets UL924. CSA or NOM Certified (see Options).

**LRP**  
Precise® Edge-Lit



**ORDERING INFORMATION**

For shortest lead times, configure products using **bolded options**.

**Example:** LRP 1 RC 120/277 EL N

Series	Housing	Number of faces	Letter color	Directional indicators	Voltage	Operation	Mounting	Options
LRP LED	<b>(blank)</b> Brushed aluminum	1 Single	RW Red on white	<b>(blank)</b> No chevrons	<b>120/277</b> Dual voltage	<b>(blank)</b> Standard non-emergency	<b>(blank)</b> Ceiling or back	<b>(blank)</b> Complete exit panel and rough-in section
	W White	2 Double	<b>RC</b> Red on clear <sup>1</sup>	LA Left <sup>1</sup>	120/347 Dual voltage <sup>4</sup>	<b>EL N</b> Nickel-cadmium battery <sup>2</sup>	EM End	<b>PNL</b> Panel assembly only
	B Black		<b>RMR</b> Red on mirror <sup>2</sup>	RA Right <sup>1</sup>		X2 Lamps wired on two separate circuits <sup>3,5</sup>	TM Top <sup>6</sup>	CSA Meets Canadian standards
	BZ Bronze		GW Green on white <sup>3</sup>	LRA Left and right		LDC6 6V DC input for LED lamp <sup>4</sup>		NOM Meets Mexican standards
	BS Brass		<b>GC</b> Green on clear <sup>1,3</sup>	DA Double-face chevrons <sup>2</sup>		LDC12/48 12-48V DC input for LED lamp <sup>4</sup>		FI Fire alarm interface <sup>3</sup>
	CR Chrome		<b>GMR</b> Green on mirror <sup>2,3</sup>					FA Flashing emergency operation and intermittent audible alarm <sup>3,7</sup>

**ADDITIONAL INFORMATION**

For additional product information, visit [www.lithonia.com](http://www.lithonia.com).






ELECTRICAL APPLICATION DATA				
TYPE	VOLTS	FACES	AMPS	WATTS
Standard LED Red	120	1	.087	1.5
Standard LED Red	120	2	.178	3.1
Standard LED Red	277	1	.089	1.8
Standard LED Red	277	2	.178	3.4
Emergency LED Red	120	1	.093	2.3
Emergency LED Red	120	2	.084	3.2
Emergency LED Red	277	1	.095	2.7
Emergency LED Red	277	2	.094	3.9
Standard LED Green	120	1	.064	1.2
Standard LED Green	120	2	.059	2.0
Standard LED Green	277	1	.062	1.3
Standard LED Green	277	2	.061	2.3
Emergency LED Green	120	1	.066	1.7
Emergency LED Green	120	2	.138	3.7
Emergency LED Green	277	1	.064	1.9
Emergency LED Green	277	2	.130	3.8

ACCESSORIES		
ORDER SEPARATELY		
LED ROUGH-IN SECTION <sup>8</sup>		
Standard	ELA LCRIS	1 or 2 faces, red or green
Standard	ELA LRIS 120 X2	1 or 2 faces, 120V w/X2 option
Standard	ELA LRIS 277 X2	1 or 2 faces, 277V w/X2 option
Emergency	ELA R LRIS 120/277 EL N	1 face, red
Emergency	ELA R 2LRIS 120/277 EL N	2 faces, red
Emergency	ELA G LRIS 120/277 EL N	1 face, green
Emergency	ELA G 2LRIS 120/277 EL N	2 faces, green
Pendant mounting (top mount only)	ELA US12	12" pendant kit with brushed aluminum canopy

Specification (add to catalog number)	Graphics	
	Back	Front
LA		<EXIT
RA		EXIT>
LRA (single face)		<EXIT>
DA	<EXIT	EXIT>
LRA (double face)	<EXIT>	<EXIT>

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.

Shipping weight: 5 lbs (2.3 kg)



**Notes**

- 1 Single-face exits only.
- 2 Mirror background simulates clear for double-face option.
- 3 Not available with CSA.
- 4 Only available with CSA. Consult specification sheet for further information.
- 5 Must specify input voltage 120 or 277.
- 6 Non-emergency exits only. No rough-in section required. Not available with LDC6 or LDC12/48.
- 7 Only available with EL N.
- 8 Supplied standard with exit unless PNL suffix is specified. Order separately only if necessary for early installation. When ordering rough-in separately, all options must be included with rough-in nomenclature (example: ELA LCRIS 120/277 FI).