

Ordering Information

AFFINITY™

Family	Finish	Options
AFN	BN Brushed Nickel	PREM Premium package - features ni-cad battery, self-diagnostics and damp location battery 0°C to 50°C (32° to 122°F)
	W White	
	B Black	EXT Exterior package - features self-diagnostics, ni-cad battery, heater, battery blanket, wet location and temperature rating of -18°C to +50°C (0°F to 122°F) ^{1,2}
	DB Dark Bronze ¹	

Accessories	
ELA AFN DPB EXT	Remote fixture to be powered by 6V battery equipment as part of an emergency lighting system

- Notes:**
- 1 Available with Exterior package and remote fixture only. Other finishes not available with the Exterior package or remote fixture.
 - 2 The Exterior package includes high temperature ni-cad batteries, wet-location rating, self-diagnostics and a temperature rating of 0oF to 122oF.

Affinity Photometrics and Performance



*Meets Life Safety Code standard minimum illuminance of 0.1 FC and average illuminance of 1.0 FC. Assumes open space with no obstructions, mounting height: 8.5', ceiling height: 9', and reflectances: 80/50/20.

