

HOLOPHANE®

ROUND CAPACITOR						
Lamp	Catalog Number	Input Voltage	Ballast A x B x C	Round Capacitor A x B	Ballast Type	Net Wt. kg (lbs)
35W HPS	RBK035HP12B	120	2.50 x 3.00 x 2.30	1.75 x 3.57	R- Reactor	2 (4)
50W HPS	RBK050HP12B	120	2.50 x 3.00 x 2.31	1.75 x 3.57	R- Reactor	2 (5)
	RBK050HP48B	480	4.00 x 2.87 x 3.00	1.75 x 3.57	HX - High Reactance	2 (5)
	RBK050HPMTB	120/208/240/277	4.00 x 2.87 x 2.69	1.75 x 3.57	HX - High Reactance - Multi-Tap	2 (5)
70W HPS	RBK070HP12B	120	2.50 x 3.00 x 2.36	1.75 x 3.94	R- Reactor	3 (6)
	RBK070HP48B	480	4.00 x 2.87 x 3.00	1.75 x 2.94	HX - High Reactance	3 (6)
	RBK070HPMTB	120/208/240/277	4.00 x 2.87 x 2.68	1.75 x 2.94	HPF Auto Multi-Tap	3 (6)
100W HPS	RBK100HP12B	120	2.50 x 3.00 x 2.59	1.75 x 3.94	R- Reactor	4 (8)
	RBK100HP48B	480	4.00 x 2.87 x 3.81	1.75 x 2.94	HX - High Reactance	4 (8)
	RBK100HPMTB	120/208/240/277	4.00 x 2.87 x 3.25	1.75 x 2.94	HPF Auto Multi-Tap	4 (8)
150W HPS 55V	RBK15AHP12B	120	2.50 x 3.00 x 3.30	1.75 x 4.81	R- Reactor	5 (10)
	RBK15AHP48B	480	4.00 x 2.87 x 4.10	1.75 x 2.94	HX - High Reactance	5 (10)
	RBK15AHPMTB	120/208/240/277	4.00 x 2.87 x 3.75	1.75 x 2.94	HPF Auto Multi-Tap	5 (10)
150W HPS 100V	RBK15BHP48B	480	4.00 x 2.87 x 3.81	1.75 x 2.94	HX - High Reactance	4 (9)
	RBK15BHPMTB	120/208/240/277	4.00 x 2.87 x 3.38	1.75 x 2.94	HPF Auto Multi-Tap	4 (9)
200W HPS	RBK200HP48B	480	4.87 x 4.25 x 3.13	1.75 x 4.81	CWA	5 (12)
	RBK200HPMTB	120/208/240/277	4.87 x 4.25 x 3.13	1.75 x 4.81	CWA - Multi-Tap	5 (12)
250W HPS	RBK250HP48B	480	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA	5 (12)
	RBK250HPMTB	120/208/240/277	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA - Multi-Tap	5 (12)
	RBK25LHP48B	480	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA (Energy Saving)	5 (12)
	RBK25LHPMTB	120/208/240/277	4.87 x 4.25 x 3.31	1.75 x 3.88	CWA - Multi-Tap (Energy Saving)	5 (12)
	RBK25RHPXXB¹	See note 1	4.87 x 4.25 x 4.63	1.75 x 3.94	Mag-Reg	7 (16)
400W HPS	RBK400HP48B	480	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA	8 (17)
	RBK400HPMTB	120/208/240/277	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA - Multi-Tap	8 (17)
	RBK40LHP48B	480	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA (Energy Saving)	8 (18)
	RBK40LHPMTB	120/208/240/277	4.87 x 4.25 x 4.31	1.75 x 4.81	CWA - Multi-Tap (Energy Saving)	8 (18)
	RBK40RHPXXB¹	See note 1	6.12 x 4.25 x 4.69	2.50 x 3.37	Mag-Reg	10 (22)
	RBK400HP48C	480	4.87 x 4.25 x 4.31	2.50 x 3.37	CWA	8 (17)
1000W HPS	RBK400HPMTC	120/208/240/277	4.87 x 4.25 x 4.31	2.50 x 3.37	CWA - Multi-Tap	8 (17)
	RBKC10HP48B	480	6.12 x 4.25 x 5.94	2.50 x 3.87	CWA	13 (28)
	RBKC10HPMTB	120/208/240/277	6.12 x 4.25 x 5.94	2.50 x 3.87	CWA - Multi-Tap	13 (28)
50W MH	RBK050MHMTB	120/208/240/277	3.94 x 2.81 x 2.91	1.75 x 2.94	CWA - Multi-Tap	3 (6)
70W MH	RBK070MHMTB	120/208/240/277	3.94 x 2.81 x 2.80	1.75 x 2.94	CWA - Multi-Tap	3 (7)
100W MH	RBK100MHMTB	120/208/240/277	3.94 x 2.81 x 2.90	1.75 x 2.94	CWA - Multi-Tap	4 (9)
150W MH	RBK150MHMTB	120/208/240/277	3.94 x 2.81 x 3.91	1.75 x 2.94	CWA - Multi-Tap	5 (10)
175W MH	RBK175MH48B	480	4.00 x 2.87 x 3.82	1.75 x 2.94	CWA	5 (10)
	RBK175MHMTB	120/208/240/277	4.00 x 2.87 x 3.68	1.75 x 2.94	CWA - Multi-Tap	5 (10)
	RBK175PM48B	480	4.00 x 2.87 x 3.82	1.75 x 2.94	CWA	5 (10)
	RBK175PMMTB	120/208/240/277	4.00 x 2.87 x 3.68	1.75 x 2.94	CWA - Multi-Tap	5 (10)
250W MH	RBK250MH48B	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA	5 (11)
	RBK250MHMTB	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap	5 (11)
	RBK25LMH48B	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA (Energy Saving)	7 (15)
	RBK25LMHMTB	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap (Energy Saving)	7 (15)
	RBK250PM48B	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA	5 (11)
	RBK250PMMTB	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap	5 (11)
	RBK25LPM48B	480	4.87 x 4.25 x 3.50	1.75 x 3.94	CWA (Energy Saving)	7 (15)
RBK25LPMMTB	120/208/240/277	4.87 x 4.25 x 3.25	1.75 x 3.94	CWA - Multi-Tap (Energy Saving)	7 (15)	
320W MH	RBK320PM48B	480	4.87 x 4.25 x 4.25	1.75 x 3.94	CWA	6 (14)
	RBK320PMMTB	120/208/240/277	4.87 x 4.25 x 4.13	1.75 x 3.94	CWA - Multi-Tap	6 (14)
350W MH	RBK350PM48B	480	4.87 x 4.25 x 4.00	1.75 x 4.25	R- Reactor	6 (14)
	RBK350PMMTB	120/208/240/277	4.87 x 4.25 x 3.66	1.75 x 4.25	R- Reactor - Multi-Tap	6 (14)
	RBK35LPM48B	480	4.87 x 4.25 x 4.00	1.75 x 4.25	CWA	6 (14)
	RBK35LPMMTB	120/208/240/277	4.87 x 4.25 x 3.66	1.75 x 4.25	CWA - Multi-Tap	6 (14)
400W MH	RBK400MH48B	480	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA	7 (15)
	RBK400MHMTB	120/208/240/277	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA - Multi-Tap	7 (15)
	RBK40LMH48B	480	4.87 x 4.25 x 4.18	1.75 x 4.81	CWA (Energy Saving)	7 (15)
	RBK40LMHMTB	120/208/240/277	4.87 x 4.25 x 3.88	1.75 x 4.81	CWA - Multi-Tap (Energy Saving)	7 (15)
	RBK40RMHXXB¹	See note 1	6.12 x 4.25 x 5.88	2.50 x 3.37	Mag Reg	11 (24)
	RBK400PM48B	480	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA	7 (15)
	RBK400PMMTB	120/208/240/277	4.87 x 4.25 x 4.25	1.75 x 4.81	CWA - Multi-Tap	7 (15)
	RBK40LPM48B	480	4.87 x 4.25 x 4.18	1.75 x 4.81	CWA (Energy Saving)	7 (15)
	RBK40LPMMTB	120/208/240/277	4.87 x 4.25 x 3.88	1.75 x 4.81	CWA - Multi-Tap (Energy Saving)	7 (15)
	RBK400MH48C	480	4.87 x 4.25 x 4.25	2.50 x 3.37	CWA	7 (15)
	RBK400MHMTC	120/208/240/277	4.87 x 4.25 x 4.25	2.50 x 3.37	CWA - Multi-Tap	7 (15)
750W MH	RBK750PM48C	480	6.125 x 4.25 x 5.12	2.50 x 3.37	CWA	11 (24)
	RBK750PMMTC	120/208/240/277	6.125 x 4.25 x 5.12	2.50 x 3.37	CWA - Multi-Tap	11 (24)
1000W	RBKC10MH48B	480	6.12 x 4.25 x 5.12	2.50 x 3.37	CWA	11 (24)
	RBKC10MH48C	480	6.12 x 4.25 x 5.12	2.50 x 3.37	CWA	11 (24)
	RBKC10MHMTC	120/208/240/277	6.12 x 4.25 x 5.12	2.50 x 3.37	CWA - Multi-Tap	11 (24)
1500W MH	RBKC15MHXXB¹	See note 1	6.12 x 4.25 x 4.50	2.50 x 4.44	CWA	15 (32)

NOTES: 1 Insert voltage 12-120V; 20-208V; 24-240V; 27-277V; or 48-480V for "XX" in catalog number
These voltages available at the same price