



Dependable Power for Any Application

# Product Datasheet

## 277/480 Primary Volts - 208/277 Secondary Volts - 1Ø Dry Type Distribution Transformer - Single Phase

Catalog #: GP123000S



### PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

### BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

---

### UL STANDARD

- UL 506

---

### CSA STANDARD

- C22.2 No. 47

---

### WARRANTY

- Acme Electric Warranty Card
- [www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

---

### GENERAL PRODUCT INFORMATION

kVA:	3.00
Primary Voltage:	277/480
Secondary Voltage:	208/277
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	11.50 (29.2)
Width (In./cm):	10.31 (26.2)
Depth (In./cm):	7.13 (18.1)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.75-1.25 (1.9-3.2)
Wiring Diagram:	78

#### PACKAGING

Ship Weight (Lbs/Kg):	58 (26.3)
-----------------------	-----------

#### COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>	

