



Dependable Power for Any Application

# Product Datasheet

## 600 Primary Volts - 120/240 Secondary Volts - Three Windings - 1Ø Dry Type Distribution Transformer - Single Phase

Catalog #: T153106



### PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

### BENEFITS

- Quiet operation with sound levels below NEMA standards

---

### UL STANDARD

- UL 506

---

### CSA STANDARD

- C22.2 No. 47

---

### WARRANTY

- Acme Electric Warranty Card
- [www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

---

### GENERAL PRODUCT INFORMATION

kVA:	0.15
Primary Voltage:	600
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	130°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	7.16 (18.2)
Width (In./cm):	3.89 (9.9)
Depth (In./cm):	3.67 (9.3)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.875 (2.2)
Wiring Diagram:	8

#### PACKAGING

Ship Weight (Lbs/Kg):	7 (3.2)
-----------------------	---------

#### COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-26
Warranty:	Acme Electric Warranty Card
<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>	

