



Dependable Power for Any Application

Product Datasheet

190/200/208/220 X 380/400/416/440 Primary Volts - 110/220
Secondary Volts - 1Ø - CE Marked
Dry Type Distribution Transformer - Single Phase

Catalog #: TF279264S



PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

CE

CE Marked

Acme Electric Warranty Card

WARRANTY

www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	7.50
Primary Voltage:	190/208/220/240 x 380/416/440/480
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	15.19 (38.6)
Width (In./cm):	13.50 (34.3)
Depth (In./cm):	10.84 (27.5)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.75-1.25 (1.9-3.2)
Wiring Diagram:	64

PACKAGING

Ship Weight (Lbs/Kg):	115 (52.2)
-----------------------	------------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
CE:	CE Marked
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf