



Actual

Catalog Number: UFSK148DB
Product ID: 7TAH006430R0002
UPC Number: 78378647430
EAN Number: 05415022244960
Status: Active

Direct Burial Splice Kits for Conductor Range 14-8 AWG

- Includes outer heat-shrink tubing insulation with adhesive sealant for rugged, water-tight protection.
- For underground feeder (UF) cable, UFSK148DB's four-in-one connector supports four-conductor, three phase-plus-neutral or single-phase wiring systems.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Includes outer heat-shrink tubing insulation with adhesive sealant for rugged, watertight protection.
Standard	UL E100543
Conductor Range	14-8 AWG
Color	Gray
Insulation	Heat Shrink Tube

Packaging

Inner Quantity	1
Inner Dimensions (inches)	12.9x6.2x1
Outer Quantity	10
Outer Dimensions (inches)	12.9x6.2x4.5
Weight Uom	23.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000186

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com