



Representative

Catalog Number: W62-1B
Product ID: 7TAA267150R0017
UPC Number: 78378633206
Status: Active

Aluminum Iridated Service Entrance Wedge Clamp and Slider for Wire Range: 2-6 ASCR, 2-6 AAAC, 1 Str.-6 Sol. , Color Code Orange

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	Blackburn
Type	Aluminum Service Wedge Clamp
Special Features	Drop wire may be cut to exact length for adjustments in drop wire sag. Can be attached to bare neutral at any point in the span. Flexible and rigid bails grip ASCR, AAC and AAAC Conductors.
Application	Dead-End Self-supporting Drop Wire. For Extremely Corrosive Areas.
Size	Length 12 inches X Depth 2-3/8 inches
Conductor Range	2-6 ASCR, 2-6 AAAC, 1 Str.-6 Sol.
Number Of Conductors	1
Material	Iridited Aluminum
Finish	Bare
Voltage Rating	35kV
Insulation	None
Mounting	Yes
Connection	Tension
Environmental Conditions	All Seasons / Conditions

Packaging

Outer Quantity	100
Outer Dimensions (inches)	13.75x8.75x9
Weight Uom	14.69 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com