

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE

Provides years of maintenance-free general illumination for residential and commercial outdoor applications such as yards, driveways, patios, loading areas and warehouses.

CONSTRUCTION

Two tool-free adjustable heads allow for easy aiming up/down or side to side. Rugged cast aluminum, corrosion-resistant housing in bronze or white. Clear acrylic lenses are fully gasketed to keep out moisture, dirt and bugs. 120V driver operates at 60Hz. Rated for outdoor installations, -40°C minimum ambient.

OPTICS

High-performance 5000K CCT LEDs produce 1096 lumens and maintain 70% of light output at 50,000 hours of service. (Nominal correlated color temperature per ANSI C78-377-2008; LED lifespan based on IESNA LM-80-08 results and calculated per IESNA TM-21-11 methodology.) An integrated photocell turns light on at dusk and off at dawn for energy savings and convenience.

INSTALLATION

Mounts easily to existing junction box on wall or under building eave. Adjustable heads allow precise illumination.

LISTINGS

UL/C-UL Certified to US and Canadian safety standards. Wet location listed for mounting higher than 4' off the ground.

WARRANTY

Five-year limited warranty. Full warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx.

NOTE: Specifications are subject to change without notice.


Actual performance may differ as a result of end-user environment and application.

Outdoor General Purpose

OFLR 6 P

DUSK-TO-DAWN LED FLOODLIGHT
2 ADJUSTABLE HEADS

High Performance LED



All dimensions are inches (centimeters).

ORDERING INFORMATION

All configurations of this product are considered "standard" and have short lead times.

Example: OFLR 6LC 120 P BZ

OFLR	6LC	120	P	
Series	Number of heads	Voltage	Features	Finish
OFLR LED floodlight	6LC 6 LEDs, 2 heads	120 120 volts	P Dusk-to-dawn photocell	BZ Bronze WH White

2-Head LED Floodlight with Photocell

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory.

