



Bus-Drop Cable Clamps - Sky-Tie™



FEATURES

- **Supports** cable up to 1-1/8" diameter. Uniform "lap" design of each clamp-half results in support along the entire quarter bend.
- **Anchors** cable for 90° angle transitions using a simple, two-piece construction of interchangeable clamp-halves.
- **Loops** excess cable for convenient handling and out-of-the-way storage, via the Sky-Tie™ SHD Duplex Converter. The SHD reduces the need to cut cable when machines are moved to new locations. The SHD converter simply fits between the two halves of the Sky-Tie™ SH cable clamps.
- Perfect For: Machine Tools, Portable Tools, Air Lines, Other heavy-cable support applications.
- **Sky-Tie™ Springs** Heavy-duty Sky-Tie™ Springs insure tautness of the cable, while absorbing vibrations and shocks. Each spring slips into the Sky-Tie™ clamp at its outside bend (or, if using the SHD Duplex, the converter's outside bend), and ties back to a structural member. Three spring models with maximum load capacities of 60, 70 and 160 pounds.



Keyhole slots permit assembly on cable without removal of bolts or threading of cable through fitting.

SKY-TIE SPRINGS					
Catalog #	Max. Spring Load	Carton		Std. Package	
		Qty.	Weight lbs.	Qty.	Weight lbs.
SHS-50	60 lbs.	10	2.2	50	11
SHS-75	70 lbs.	10	2.7	50	14
SHS-1125	160 lbs.	10	11	10	11

SKY-TIE TWO-IN-ONE CABLE CLAMPS						
Catalog #	Conduit Size (in.)	Typical Multi-Conductor Cable Size	Carton		Std. Package	
			Qty.	Weight lbs.	Qty.	Weight lbs.
SH-50	1/2-3/4	14/4 thru 8/4	10	3.5	50	18.5
SH-75	3/4 to 1 1/8	8/4 thru 3/4 or (1) 500 MCM	10	7	50	36
SH-1125	1 1/2 to 1 1/16	Special Applications	5	10	25	50

SKY-TIE "DUPLEX" COMPONENT						
Catalog #	Conduit Size (in.)	Typical Multi-Conductor Cable Size	Carton		Std. Package	
			Qty.	Weight lbs.	Qty.	Weight lbs.
SHD-50	1/2 to 3/4	14/4 thru 3/4	10	3.25	50	17.25
SHD-75	3/4 to 1 1/2	8/4 thru 3/4 or (1) 500 MCM	10	7	50	36