

Industrial Wireless AP/CPE

Accessories



Advantech P/N	ANT-5115-AE	ANT-5130-AE	ANT-5210-AE	ANT-5230-AE	ANT-5260-AE	ANT-5290-AE
Description	1.5M N-Plug to SMA-Plug cable	3M N-Plug to SMA-Plug cable	1M N-Plug to N-Plug cable	3M N-Plug to N-Plug cable	6M N-Plug to N-Plug cable	9M N-Plug to N-Plug cable
Cable Type	ULA-168	ULA-168	ULA400	ULA400	ULA400	ULA400
VSWR	1.5 : 1 Max.@ DC ~ 3.0 GHz 2.0 : 1 Max.@ 3.0 ~ 6.0 GHz	1.5 : 1 Max.@ DC ~ 3.0 GHz 2.0 : 1 Max.@ 3.0 ~ 6.0 GHz	1.5 : 1 Max.@ DC ~ 6.0 GHz	1.5 : 1 Max.@ DC ~ 6.0 GHz	1.5 : 1 Max.@ DC ~ 6.0 GHz	1.5 : 1 Max.@ DC ~ 6.0 GHz
Insertion loss	2.0 dB Max.@ DC ~ 3.0 GHz 2.5 dB Max.@ 3.0 ~ 6.0 GHz	3.5 dB Max.@ DC ~ 3.0 GHz 4 dB Max.@ 3.0 ~ 6.0 GHz	0.7 dB Max.@ DC ~ 3 GHz 1.0 dB Max.@ 3 ~ 6.0 GHz	1.1 dB Max.@ DC ~ 3 GHz 1.6 dB Max.@ 3 ~ 6.0 GHz	1.8 dB Max.@ DC ~ 3 GHz 2.7 dB Max.@ 3 ~ 6.0 GHz	3.0 dB (Max.) @ DC ~ 3 GHz 4.0 dB (Max.) @ 3 ~ 6 GHz
Connector Type	N-plug to RP SMA-plug	N-plug to RP SMA-plug	N-plug to N-plug	N-plug to N-plug	N-plug to N-plug	N-plug to N-plug
Cable Length	1.5M	3M	1M	3M	6M	9M



Advantech P/N	ANT-5501-AE	ANT-5502-AE	ANT-5601-AE
Description	1KV Surge Arrestor N-Jack to N-Jack	1KV Surge Arrestor N-Plug to N-Jack	Bulkhead adapter N-Jack to N-Jack
Surge Protection	1KV	1KV	N/A
VSWR	1.25: 1 Max @ DC ~ 4GHz 1.45: 1 Max @ 4 ~ 6GHz	1.3: 1 Max @ DC ~ 4GHz 1.5: 1 Max @ 4 ~ 6GHz	1.2: 1 Max @ DC ~ 3GHz 1.4: 1 Max @ 3 ~ 6GHz
Insertion loss	0.8 dB	0.8 dB	N/A
Connector Type	N Jack to N Jack	N plug to N Jack	N-jack to N-jack