



**Specifications**

**Single Element Units (EXS)**

Model	Watts	Volts	Amps	Overall Length Inches	Replacement Part No.
EXS801	800	120	6.7	24	HE8120
EXS802	800	240	3.3	24	HE8240
EXS1101	1100	120	9.2	30	HE11120
EXS1102	1100	240	4.6	30	HE11240
EXS1802	1800	240	7.5	46	HE18240
EXS1804	1800	480	3.8	46	HE18480
EXS2502	2500	240	10.4	60	HE25240
EXS2504	2500	480	5.2	60	HE25480
EXS3002	3000	240	12.5	72	HE30240
EXS3004	3000	480	6.3	72	HE30480
EXS3602	3600	240	15.0	86	HE36240
EXS3604	3600	480	7.5	86	HE36480

**Double Element Units (EXD)**

Model	Watts	Volts	Amps	Overall Length Inches	Replacement Part No.
EXD1601	1600	120	13.3	24	HE8120
EXD1602	1600	240	6.7	24	HE8240
EXD2201	2200	120	18.3	30	HE11120
EXD2202	2200	240	9.2	30	HE11240
EXD3602	3600	240	15.0	46	HE18240
EXD3604	3600	480	7.5	46	HE18240
EXD5002	5000	240	20.8	60	HE25240
EXD5004	5000	480	10.4	60	HE25240
EXD6002	6000	240	25.0	72	HE30240
EXD6004	6000	480	12.5	72	HE30240
EXD7202	7200	240	30.0	86	HE36240
EXD7204	7200	480	15.0	86	HE36240

**Moisture Resistant Process Modules**

Model	Watts	Volts	Amps	Overall Length Inches	Replacement Part No.
OH2028-H3	2000	208	9.6	26.25"	HE20208
OH202-H3	2000	240	8.3	26.25"	HE20240
OH204-H3	2000	480	4.2	26.25"	HE20480
OH205-H3	2000	550	3.6	26.25"	HE20550
OH4528-H3	4500	208	21.6	47.25"	HE45208
OH452-H3	4500	240	18.8	47.25"	HE45240
OH454-H3	4500	480	9.4	47.25"	HE45480
OH455-H3	4500	550	8.2	47.25"	HE45550