



Representative

**Catalog Number:** WR239  
**Product ID:** 7TAA267110R0009  
**UPC Number:** 78378610013  
**Status:** Active

Aluminum Wide Range H-Type Compression Connector Main: 2/0 - 1/0 ACSR, 2/0 - 1/0 Str., Tap: 2-4 ACSR, 1-3 Str., 1-2 Sol., Die: D, D3

### North American Specifications (UNSPSC)

UNSPSC	39121409 Wire connectors
IGCC	4543 Wire connectors
Brand Name	Blackburn
Type	Wide-Range Tap Connector
Special Features	Made of 1350 Aluminum Alloy for high strength and high conductivity. Standard Compression tools and dies install all sizes - no special tools needed. Field-proven ribbed design enables excellent connector/conductor contact without distorting the conductor's shape. Fold-in tabs provide tab interlock as tool closes. Prefilled with oxide inhibitor held captive in the rib/connection area.
Application	For Combinations of Aluminum to Aluminum and Aluminum to Copper Conductors.
Standard	RUS Accepted. Complies with ANSI C119.4 Specifications
Size	Length 1-7/8 inch
Connection	Compression/ Crimp
Wire Size	Main: 2/0 - 1/0 ACSR, 2/0 - 1/0 Stranded, Tap: 2-4 ACSR, 1-3 Stranded, 1-2 Solid
Number Of Conductors	2
Material	Aluminum
Voltage Rating	None since Uninsulated
Insulation	None
Temperature Rating	up to 90 Degrees C.
Mounting	None
Environmental Conditions	All Seasons / Conditions

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	13.1x5.6x2.7
Outer Quantity	250
Outer Dimensions (inches)	14.5x14.5x12
Weight Uom	15 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)