

# JK LIGHTING SYSTEMS

NEW FLUORESCENT LIGHTING FIXTURES AND CONVERSIONS

P.O BOX 8867  
STOCKTON, CA 95208  
(209) 464-7539



1707 EL PINAL  
STOCKTON, CA 95205  
FAX (209) 464-8656



## HINGED FIXTURE EXAMPLE & INSTALLATION

- ☆ Ballast cover and socket plate units are die formed using 22 GA Cold Rolled Steel with a high gloss, white baked enamel finish, minimum reflectance 85%.
- ☆ Continuous type hinge allows ease of installation and future accessibility.
- ☆ Snap-in type rotor lamp sockets allow lamps to be locked into place simply by twisting lamp 1/4 turn.
- ☆ All wire is 18 GA. solid core, rated 600v., utilizing wire trap type connectors for a positive connection.
- ☆ All attachment hardware included.


☆☆☆  
PATENT



MANUFACTURED  
AND ASSEMBLED IN  
THE UNITED STATES


CUSTOM MADE TO FIT  
YOUR  
FIXTURES

Please Give Us  
your outside to outside width  
measurements at time of order



### INSTALLATION AS EASY AS 1 2 3

- 1 STRIP EXISTING FIXTURE BY REMOVING ALL DETACHABLE PARTS INCLUDING WIRING AND BALLAST. LEAVE END PLATES ATTACHED.
- 2 PLACE HINGED BALLAST COVER FLUSH WITH BARE FIXTURE. ATTACH HINGE SIDE TO FIXTURE WITH TECH SCREWS. ALLOW UNIT TO SWING DOWN.
- 3 CONNECT DRIVER POWER LEADS TO EXISTING POWER SUPPLY SWING UNIT UP AND SECURE FLANGE TO SIDE OF CAN WITH TECH SCREWS.



## JK RETRO-FIT COMPLETE !!!



Typical ordering number

JK-TLED-C-S-1804-H-AMW

Prefix	Lamp Type Wattage	Wire Options	Can Size	Series No.	Type	Reflector Options
JK	TLED = Tubular LED	JK WILL PREWIRE RETROFIT UNIT FOR YOUR LED LAMP DRIVER	S = 2 1/2" to 5" M = 5 1/16" to 7" L = 7 1/16" to 12"	1401 = 1 Lamp 1402 = 2 Lamp 1403 = 3 Lamp 1802 = 2 Lamp 1804 = 4 Lamp 1806 = 6 Lamp	H = Hinge H - W = Hinged Wing Industrial Type	AM = Ambrite OPT = Optibrite AMW = Amwhite 90+ WW = WALL WASH