

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L2				1492-L2T				1492-L2Q			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
Specifications	<i>Feed-through terminal block</i>				<i>Feed-through terminal block with 2 connection points on one side</i>				<i>Feed-through terminal block with 2 connection points per side</i>			
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	300V AC/DC		500V AC/DC	550V AC/DC	300V AC/DC		500V AC/DC	550V AC/DC	300V AC/DC		500V AC/DC	550V AC/DC
Maximum Current	15 A	20 A	17.5 A	15 A	15 A	20 A	17.5 A	15 A	15 A	20 A	17.5 A	15 A
Wire Range (Rated Cross Section)	#26...14 AWG		1.5 mm ²	1.5 mm ²	#26...14 AWG		1.5 mm ²	1.5 mm ²	#26...14 AWG		1.5 mm ²	1.5 mm ²
Wire Strip Length	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)			
Density	87 pcs/ft (285 pcs/m)				87 pcs/ft (285 pcs/m)				87 pcs/ft (285 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Terminal Blocks		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.
Color	Grey	1492-L2		50		1492-L2T		50		1492-L2Q		50
	Red	1492-L2-RE		50		1492-L2T-RE		50		1492-L2Q-RE		50
	Blue	1492-L2-B		50		1492-L2T-B		50		1492-L2Q-B		50
	Black	1492-L2-BL		50		1492-L2T-BL		50		1492-L2Q-BL		50
	Green	1492-L2-G		50		1492-L2T-G		50		1492-L2Q-G		50
	Yellow	1492-L2-Y		50		1492-L2T-Y		50		1492-L2Q-Y		50
	Orange	1492-L2-OR		50		1492-L2T-OR		50		1492-L2Q-OR		50
	Brown	1492-L2-BR		50		1492-L2T-BR		50		1492-L2Q-BR		50
	White	1492-L2-W		50		1492-L2T-W		50		1492-L2Q-W		50
Accessories		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.		Cat. No.		Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)		199-DR1		10		199-DR1		10		199-DR1		10
1 m Symmetrical DIN (Aluminum)		1492-DR5		10		1492-DR5		10		1492-DR5		10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6		2		1492-DR6		2		1492-DR6		2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7		2		1492-DR7		2		1492-DR7		2
End Barriers	Grey	1492-EBL2		50		1492-EBL2T		50		1492-EBL2Q		50
	Blue	1492-EBL2-B		50		1492-EBL2T-B		50		1492-EBL2Q-B		50
	Yellow	1492-EBL2-Y		50		1492-EBL2T-Y		50		1492-EBL2Q-Y		50
End Anchors and Retainers												
Screwless End Retainer		1492-ERL35		20		1492-ERL35		20		1492-ERL35		20
DIN Rail — Normal Duty		1492-EAJ35		100		1492-EAJ35		100		1492-EAJ35		100
DIN Rail — Heavy Duty		1492-EAHJ35		50		1492-EAHJ35		50		1492-EAHJ35		50
Jumpers												
Plug-in Center Jumper — 10-Pole		1492-CJL4-10		20		1492-CJL4-10		20		1492-CJL4-10		20
Plug-in Center Jumper — 5-Pole		1492-CJL4-5		60		1492-CJL4-5		60		1492-CJL4-5		60
Plug-in Center Jumper — 4-Pole		1492-CJL4-4		60		1492-CJL4-4		60		1492-CJL4-4		60
Plug-in Center Jumper — 3-Pole		1492-CJL4-3		60		1492-CJL4-3		60		1492-CJL4-3		60
Plug-in Center Jumper — 2-Pole		1492-CJL4-2		60		1492-CJL4-2		60		1492-CJL4-2		60
Other Accessories												
Reducing Sleeves #28...#24 AWG (0.13...0.2 mm ²) White		1492-PSL2-2		100		1492-PSL2-2		100		1492-PSL2-2		100
Reducing Sleeves #22...#20 AWG (0.25...0.5 mm ²) Grey		1492-PSL2-5		100		1492-PSL2-5		100		1492-PSL2-5		100
Test Plug (Stackable)		1492-TPL4		25		1492-TPL4		25		1492-TPL4		25
Electrical Warning Plate		1492-EWPL4		20		1492-EWPL4		20		1492-EWPL4		20
Marking Systems												
Snap-In Marker Cards		1492-M3X12 (120/card)		5		1492-M3X12 (120/card)		5		1492-M3X12 (120/card)		5
Snap-In Marker Cards		1492-M3X5 (100/card)		5		1492-M3X5 (100/card)		5		1492-M3X5 (100/card)		5



Spring-Clamp Connection Terminal Blocks

Multi-Circuit Feed-Through Blocks

	1492-LD2			1492-LD3				1492-L3QS			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.											
Specifications	<i>Two-circuit feed-through terminal block</i>			<i>Two-circuit feed-through terminal block</i>				<i>Side-by-side two circuit terminal block</i>			
Certifications		CSA	IEC		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	300V AC/DC	600V AC/DC	500V AC/DC	600V AC/DC	600V AC/DC	800V AC/DC	550V AC/DC	600V AC/DC	600V AC/DC	800V AC/DC	550V AC/DC
Maximum Current	10 A		17.5 A	20 A	25 A	24 A	20 A	25 A	27 A	24 A	21 A
Wire Range (Rated Cross Section)	#28... 16 AWG		1.5 mm ²	#30... 12 AWG		2.5 mm ²	0.5...2.5 mm ² (#20...14 AWG)	#26... 12 AWG		2.5 mm ²	2.5 mm ² (20... 12 AWG)
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)				0.39 in. (10 mm)			
Density	87 pcs/ft (285 pcs/m)			59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Pkg Qty.
Color	Grey	1492-LD2	50	1492-LD3	25	1492-L3QS	50	50	Grey	50	50
	Red	1492-LD2-RE	50	1492-LD3-RE	25	1492-L3QS-RE	50	50	Red	50	50
	Blue	1492-LD2-B	50	1492-LD3-B	25	1492-L3QS-B	50	50	Blue	50	50
	Black	1492-LD2-BL	50	1492-LD3-BL	25	1492-L3QS-BL	50	50	Black	50	50
	Green	1492-LD2-G	50	1492-LD3-G	25	1492-L3QS-G	50	50	Green	50	50
	Yellow	1492-LD2-Y	50	1492-LD3-Y	25	1492-L3QS-Y	50	50	Yellow	50	50
	Orange	1492-LD2-OR	50	1492-LD3-OR	25	1492-L3QS-OR	50	50	Orange	50	50
	Brown	1492-LD2-BR	50	1492-LD3-BR	25	1492-L3QS-BR	50	50	Brown	50	50
	White	1492-LD2-W	50	1492-LD3-W	25	1492-L3QS-W	50	50	White	50	50
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Pkg Qty.
Mounting Rails											
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10	199-DR1	10	199-DR1	10	10
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10	1492-DR5	10	1492-DR5	10	10
1 m Hi-Rise Symmetrical DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2	1492-DR6	2	1492-DR6	2	2
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2	1492-DR7	2	1492-DR7	2	2
End Barriers											
Grey	1492-EBLD2	50	1492-EBLD3	20	1492-EBL3Q	50	1492-EBL3Q	50	1492-EBL3Q	50	50
Blue	1492-EBLD2-B	20	1492-EBLD3-B	20	1492-EBL3Q-B	50	1492-EBL3Q-B	50	1492-EBL3Q-B	50	50
Yellow	1492-EBLD2-Y	20	1492-EBLD3-Y	20	1492-EBL3Q-Y	50	1492-EBL3Q-Y	50	1492-EBL3Q-Y	50	50
End Anchors and Retainers											
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20	20
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100	100
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50	50
Jumpers											
Plug-in Center Jumper — 50-Pole	—	—	1492-CJK5-50	10	—	—	—	—	—	—	—
Plug-in Center Jumper — 10-Pole	1492-CJL4-10	20	1492-CJK5-10	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 9-Pole	—	—	1492-CJK5-9	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 8-Pole	—	—	1492-CJK5-8	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 7-Pole	—	—	1492-CJK5-7	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 6-Pole	—	—	1492-CJK5-6	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 5-Pole	1492-CJL4-5	60	1492-CJK5-5	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 4-Pole	1492-CJL4-4	60	1492-CJK5-4	60	—	—	—	—	—	—	—
Plug-in Center Jumper — 3-Pole	1492-CJL4-3	60	1492-CJK5-3	60	—	—	—	—	—	—	—
Plug-in Center Jumper — 2-Pole	1492-CJL4-2	60	1492-CJK5-2	60	—	—	—	—	—	—	—
Other Accessories											
Reducing Sleeves #28...24 AWG (0.13...0.2 mm ²)	1492-PSL2-2	100	1492-PSLS2-2	100	1492-PSL3-2	100	1492-PSL3-2	100	1492-PSL3-2	100	100
Reducing Sleeves #22...20 AWG (0.25...0.5 mm ²)	1492-PSL2-5	100	1492-PSLS2-5	100	1492-PSL3-5	100	1492-PSL3-5	100	1492-PSL3-5	100	100
Reducing Sleeves #18 AWG (0.75...1.0 mm ²)	—	—	—	—	1492-PSL3-10	100	1492-PSL3-10	100	1492-PSL3-10	100	100
Test Plug	1492-TPL4	25	—	—	1492-TP23	20	1492-TP23	20	1492-TPL5	25	25
Electrical Warning Plate	1492-EWPL4	20	—	—	1492-EWPL5	20	1492-EWPL5	20	1492-EWPL5	20	20
Marking Systems											
Snap-In Marker Cards	1492-M3X12 (120/card)*	5	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5	1492-M5X5 (200/card)	5	5
	1492-M3X5 (100/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-MH5X10 (96/card)	5	5
Hinged Marker Cards	—	—	—	—	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5	5

* May only be mounted in terminal block corner marking positions.



Spring-Clamp Connection Terminal Blocks

Specialty Feed-Through Blocks

	1492-LD2C			1492-LD3C				1492-LD4C		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.										
Specifications	Two-level feed-through terminal block with commoning bar			Two-level feed-through terminal block with commoning bar				Two-level feed-through terminal block with commoning bar		
Certifications		CSA	IEC		CSA	IEC	ATEX		CSA	IEC
Voltage Rating	300V AC/DC	600V AC/DC	500V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC
Maximum Current	10 A		17.5 A	20 A	25 A	24 A	22 A	25 A	30 A	32 A
Wire Range (Rated Cross Section)	#28...16 AWG		1.5 mm ²	#30...12 AWG		2.5 mm ²	0.5...2.5 mm ² (#20...14 AWG)	#26...10 AWG		4 mm ²
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)				0.39 in. (10 mm)		
Density	87 pcs/ft (285 pcs/m)			59 pcs/ft (196 pcs/m)				49 pcs/ft (163 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)		
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color: Grey	1492-LD2C	50	1492-LD3C	25	1492-LD4C	25				
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails:										
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10				
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10				
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2				
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2				
End Barriers Grey	1492-EBLD2	50	1492-EBLD3	20	1492-EBLD4	20				
End Anchors and Retainers										
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20				
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100				
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50				
Jumpers:										
Plug-in Center Jumper — 50-Pole	—	—	1492-CJK5-50	10	—	—				
Plug-in Center Jumper — 10-Pole	1492-CJL4-10	20	1492-CJK5-10	20	1492-CJK6-10	20				
Plug-in Center Jumper — 9-Pole	—	—	1492-CJK5-9	20	1492-CJK6-9	20				
Plug-in Center Jumper — 8-Pole	—	—	1492-CJK5-8	20	1492-CJK6-8	20				
Plug-in Center Jumper — 7-Pole	—	—	1492-CJK5-7	20	1492-CJK6-7	20				
Plug-in Center Jumper — 6-Pole	—	—	1492-CJK5-6	20	1492-CJK6-6	20				
Plug-in Center Jumper — 5-Pole	1492-CJL4-5	60	1492-CJK5-5	20	1492-CJK6-5	20				
Plug-in Center Jumper — 4-Pole	1492-CJL4-4	60	1492-CJK5-4	60	1492-CJK6-4	60				
Plug-in Center Jumper — 3-Pole	1492-CJL4-3	60	1492-CJK5-3	60	1492-CJK6-3	60				
Plug-in Center Jumper — 2-Pole	1492-CJL4-2	60	1492-CJK5-2	60	1492-CJK6-2	60				
Other Accessories:										
Reducing Sleeves 28...24 AWG (0.13...0.2 mm ²) White	1492-PSL2-2	100	1492-PSLS2-2	100	—	—				
Reducing Sleeves 22...20 AWG (0.13...0.2 mm ²) Grey	1492-PSL2-5	100	1492-PSLS2-5	100	—	—				
Test Plug	1492-TPL4	25	—	—	1492-TP23	20				
Electrical Warning Plate	1492-EWPL4	20	—	—	1492-EWPL6	20				
Marking Systems:										
Snap-In Marker Cards	1492-M3X12 (120/card)*	5	1492-M5X10 (144/card)	5	1492-M6X10 (120/card)	5				
Snap-In Marker Cards	1492-M3X5 (100/card)	5	1492-M5X5 (200/card)	5	1492-M6X5 (200/card)	5				

* May only be mounted in terminal block corner marking positions.



Screwless Center Jumpers



For Use With	Color	Pkg Qty.	Cat. No.
1492-L2..., L2T, L2Q, LD2, LD2C	Yellow	60	1492-CJL4-2
		60	1492-CJL4-3
		60	1492-CJL4-4
		60	1492-CJL4-5
		20	1492-CJL4-10
1492-LM3, LC3, LDC3, LDAG3, LDG3P, JKD3..., J3P..., J3, J3TW (see Note)	Yellow	60	1492-CJLJ5-2
	Red	60	1492-CJLJ5-2-R
	Blue	60	1492-CJLJ5-2-B
	Black	60	1492-CJLJ5-2-BL
	Yellow	60	1492-CJLJ5-3
	Red	60	1492-CJLJ5-3-R
	Blue	60	1492-CJLJ5-3-B
	Black	60	1492-CJLJ5-3-BL
	Yellow	60	1492-CJLJ5-4
		20	1492-CJLJ5-5
		20	1492-CJLJ5-6
		20	1492-CJLJ5-7
		20	1492-CJLJ5-8
		20	1492-CJLJ5-9
		20	1492-CJLJ5-10
	Red	20	1492-CJLJ5-10-R
	Blue	20	1492-CJLJ5-10-B
	Black	20	1492-CJLJ5-10-BL
	White	20	1492-CJLJ5-10-W
	Yellow	10	1492-CJLJ5-50
Red	10	1492-CJLJ5-50-R	
Blue	10	1492-CJLJ5-50-B	
Black	10	1492-CJLJ5-50-BL	
White	10	1492-CJLJ5-50-W	

For Use With	Pkg Qty.	Cat. No.
1492-RFB4	10	1492-CJR8-2
	10	1492-CJR8-3
	10	1492-CJR8-4
	10	1492-CJR8-5
	10	1492-CJR8-6
	10	1492-CJR8-7
	10	1492-CJR8-8
	10	1492-CJR8-9
	10	1492-CJR8-10
	1492-RAFB4	10
10		1492-CJRA10-3
10		1492-CJRA10-4
10		1492-CJRA10-5

For Use With	Color	Pkg Qty.	Cat. No.
1492-J4, J4M (see Note)	Yellow	60	1492-CJLJ6-2
	Red	60	1492-CJLJ6-2-R
	Blue	60	1492-CJLJ6-2-B
	Black	60	1492-CJLJ6-2-BL
	Yellow	60	1492-CJLJ6-3
	Red	60	1492-CJLJ6-3-R
	Blue	60	1492-CJLJ6-3-B
	Black	60	1492-CJLJ6-3-BL
	Yellow	60	1492-CJLJ6-4
	Yellow	20	1492-CJLJ6-10
	Red	20	1492-CJLJ6-10-R
	Blue	20	1492-CJLJ6-10-B
	Black	20	1492-CJLJ6-10-BL
	Yellow	10	1492-CJLJ6-41
1492-L6, L6T, L16D	Yellow	60	1492-CJL8-2
		60	1492-CJL8-3
		60	1492-CJL8-4
		10	1492-CJL8-32
1492-L10	Yellow	25	1492-CJL10-2
1492-L16	Yellow	25	1492-CJL12-2
1492-L35	Yellow	10	1492-CJL16-2
1492-L3, L3T, L3Q, L3P, LD3, LD3C, LKD3, LTF3, LS2..., L16D	Yellow	60	1492-CJK5-2
		60	1492-CJK5-3
		60	1492-CJK5-4
		20	1492-CJK5-5
		20	1492-CJK5-6
		20	1492-CJK5-7
		20	1492-CJK5-8
		20	1492-CJK5-9
		20	1492-CJK5-10
		10	1492-CJK5-50
1492-L4, L4T, L4Q, LD4DF, LD4DR, LD4SS, LD4, LD4C, L16D	Yellow	60	1492-CJK6-2
		60	1492-CJK6-3
		60	1492-CJK6-4
		20	1492-CJK6-5
		20	1492-CJK6-6
		20	1492-CJK6-7
		20	1492-CJK6-8
		20	1492-CJK6-9
		20	1492-CJK6-10
		20	1492-CJK6-20