


NOTES:

1. MEASURE THICKNESS OF FLAT PLATE (DISREGARD PINS PROTRUDING FROM SURFACE).

1492-EBJP3	A	—	PN-167796	GRAY	1.4	44.5	87.5	1000333166	BOX	50	155x134x45	41110-194
1492-BKJC3	A	2	N/A	GRAY	2.5	36.7	45	42164-552-01 42164-552-02	BOX	1 KIT <sup>1</sup>	117x96x40	41110-194
1492-BKJDC3	A	2	N/A	GRAY	2.5	45.2	58	42164-552-03 42164-552-04	BOX	1 KIT <sup>2</sup>	117x96x40	41110-194
1492-EBJ3	A	2	N/A	GRAY	1.5	33.35	60	42164-552-05	BOX	50	157x100x44	41110-194
1492-EBJ3-B	A	2	N/A	BLUE	1.5	33.35	60	42164-552-05	BOX	50	157x100x44	41110-194
1492-EBJ3-Y	A	2	N/A	YELLOW	1.5	33.35	60	42164-552-05	BOX	50	157x100x44	41110-194
1492-EBJ3TM	A	1	N/A	GRAY	1.5	61.25	87.8	42164-622-03	BOX	20	181x168x50	41110-194
1492-EBJ4CTB	A	1	N/A	GRAY	2.0	38.00	55	42164-552-12	BOX	50	219x168x50	41110-194
1492-EBJ4Q	A	1	N/A	GRAY	1.5	41	62	42164-552-10	BOX	50	221X138X70	41110-194
1492-EBJ4Q-Y	A	1	N/A	YELLOW	1.5	41	62	42164-552-10	BOX	50	221X138X70	41110-194
1492-EBJ4TW	A	1	N/A	GRAY	1.5	41	69	42164-552-11	BOX	50	221X138X70	41110-194
1492-EBJ4TW-Y	A	1	N/A	YELLOW	1.5	41	69	42164-552-11	BOX	50	221X138X70	41110-194
1492-EBJ16	A	2	N/A	GRAY	1.5	49	60	42164-552-06	BOX	20	117x96x40	41110-194
1492-EBJ16-B	A	2	N/A	BLUE	1.5	49	60	42164-552-06	BOX	20	117x96x40	41110-194
1492-EBJ16-Y	A	2	N/A	YELLOW	1.5	49	60	42164-552-06	BOX	20	117x96x40	41110-194
1492-EBJD3	A	2	N/A	GRAY	1.5	54.5	69	42164-552-07	BOX	20	117x96x40	41110-194
1492-EBJD3-B	A	2	N/A	BLUE	1.5	54.5	69	42164-552-07	BOX	20	117x96x40	41110-194
1492-EBJD3-Y	A	2	N/A	YELLOW	1.5	54.5	69	42164-552-07	BOX	20	117x96x40	41110-194
1492-EBJD3FB	A	1	N/A	GRAY	1.5	40.5	73.7	42164-552-13	BOX	20	135x133x45	41110-194
1492-EBJD3P	A	2	N/A	GRAY	1.5	58.8	80.2	42164-552-09	BOX	20	117x96x40	41110-194
1492-EBJD4	A	1	N/A	GRAY	1.5	53.9	60	42164-622-01	BOX	20	169x96x42	41110-194
1492-EBJD4-B	A	1	N/A	BLUE	1.5	53.9	60	42164-622-01	BOX	20	169x96x42	41110-194
1492-EBJD4-Y	A	1	N/A	YELLOW	1.5	53.9	60	42164-622-01	BOX	20	169x96x42	41110-194
1492-EBJO	A	2	N/A	GRAY	2.5	39.2	56	42164-552-08	BOX	20	91x72x41	41110-194
1492-EBJS4	A	1	N/A	GRAY	2.0	31.0	59.5	42164-622-02	BOX	50	219x168x50	41110-194
1492-EBTF3	B	1	N/A	GRAY	1.5	48	90.7	42164-602-01	BOX	50	162x115x58	41110-194
1492-EBTS3	B	1	N/A	GRAY	1.5	48	67.6	42164-602-02	BOX	50	139x115x50	41110-194
1492-N37	B	1	N/A	BLACK	2.5	48.4	71.1	42164-602-03	BOX	50	130x108x56	41110-194
<b>CATALOG NUMBER</b>	<b>SERIES LETTER</b>	<b>CHG. CHAR.</b>	<b>MATERIAL NUMBER</b>	<b>PLASTIC COLOR</b>	<b>THICKNESS (mm) +/-0.3</b>	<b>HEIGHT (mm) +/-1.0</b>	<b>WIDTH (mm) +/-1.0</b>	<b>IDENTIFICATION PER:</b>	<b>PACKAGE TYPE</b>	<b>PACKAGE QTY.</b>	<b>INSIDE DIMENSIONS OF CARTON (mm), REF</b>	<b>CARTON LABEL</b>

<sup>1</sup> 1 KIT OF BKJC3 = 10 PCS EBJC3 + 10 PCS SBJC3  
<sup>2</sup> 1 KIT OF BKJDC3 = 10 PCS EBJDC3 + 10 PCS SBJDC3

NOTICE  
 ALLEN-BRADLEY SHALL BE NOTIFIED IMMEDIATELY OF ANY PROPOSED CHANGES IN MATERIALS OR PROCESSES WHICH WOULD AFFECT THE PERFORMANCE, RELIABILITY, OR PHYSICAL CHARACTERISTICS OF THIS DEVICE. IN THE EVENT OF NON-CONFORMANCE, VENDORS SHALL BE INFORMED OF THE TEST METHODS USED TO DETERMINE REJECTION AND SHALL BE REQUIRED TO ADJUST DEFICIENCIES.

REFERENCE		REVISION AUTHORIZATION		DIMENSIONS APPLY BEFORE SURFACE TREATMENT  (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED	END BARRIERS FOR BULLETIN 1492-J TERMINAL BLOCKS		E-DOC	
1	1003114	2	1005776		.XX: ± .02	 <b>Allen-Bradley</b>		THIS DRAWING IS THE PROPERTY OF ROCKWELL AUTOMATION, INC. OR ITS SUBSIDIARIES AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY ROCKWELL AUTOMATION, INC.  LOCATION: MILWAUKEE, WISCONSIN U.S.A.
3	1025925	04	10050100	.XXX: ± .005				
46010				ANGLES: ± N/A	DR. J. VELIQUETTE	DATE 02-24-04	DWG. SIZE	SHEET 1 OF 1
					CHKD. J.HUBACEK	DATE 11-15-06	B	40164-880
					APPD. J.HUBACEK	DATE 11-15-06		