

## End Barriers

End barriers are required to provide the necessary insulation for the last terminal block in a group.

Dimensions Width x Length x Height	For Use With	Color	Pkg Qty.	Cat. No.
0.08 x 1.14 x 2.03 in. (2 x 28.9 x 51.5 mm)	1492-L2, LG2	Grey	50	<b>1492-EBL2</b>
		Blue	50	<b>1492-EBL2-B</b>
		Yellow	50	<b>1492-EBL2-Y</b>
0.08 x 1.14 x 2.48 in. (2 x 28.9 x 63 mm)	1492-L2T, LG2T	Grey	50	<b>1492-EBL2T</b>
		Blue	50	<b>1492-EBL2T-B</b>
		Yellow	50	<b>1492-EBL2T-Y</b>
0.08 x 1.14 x 2.95 in. (2 x 28.9 x 75 mm)	1492-L2Q, LG2Q	Grey	50	<b>1492-EBL2Q</b>
		Blue	50	<b>1492-EBL2Q-B</b>
		Yellow	50	<b>1492-EBL2Q-Y</b>
0.08 x 1.15 x 2.34 in. (2 x 29.1 x 59.5 mm)	1492-L3, LG3, LKD3, L3P	Grey	50	<b>1492-EBL3</b>
		Blue	50	<b>1492-EBL3-B</b>
		Yellow	50	<b>1492-EBL3-Y</b>
0.08 x 1.20 x 2.54 in. (2 x 30.6 x 64.5 mm)	1492-L3T, LG3T	Grey	50	<b>1492-EBL3T</b>
		Blue	50	<b>1492-EBL3T-B</b>
		Yellow	50	<b>1492-EBL3T-Y</b>
0.08 x 1.20 x 3.11 in. (2 x 30.6 x 79 mm)	1492-L3Q, L3QS, LG3Q	Grey	50	<b>1492-EBL3Q</b>
		Blue	50	<b>1492-EBL3Q-B</b>
		Yellow	50	<b>1492-EBL3Q-Y</b>
0.10 x 1.06 x 2.8 in. (2.5 x 27 x 71 mm)	1492-L31P, 1492-LG31P	Yellow	50	<b>1492-EBL31P-Y</b>
	1492-L3T1P, 1492-LG3T1P	Grey	50	<b>1492-EBL3T1P</b>
		Yellow	50	<b>1492-EBL3T1P-Y</b>
0.08 x 1.20 x 3.11 in. (2 x 30.6 x 79 mm)	1492-L3Q2P	Grey	50	<b>1492-EBL3Q2P</b>
0.10 x 1.76 x 3.17 in. (2.5 X 44.7 x 80.5)	1492-LD32P	Grey	50	<b>1492-EBLD32P</b>
0.08 x 1.37 x 2.44 in. (2 x 34.85 x 62 mm)	1492-L4, LG4	Grey	50	<b>1492-EBL4</b>
		Blue	50	<b>1492-EBL4-B</b>
		Yellow	50	<b>1492-EBL4-Y</b>
0.08 x 1.37 x 3.31 in. (2 x 34.85 x 84 mm)	1492-L4T, LG4T	Grey	50	<b>1492-EBL4T</b>
		Blue	50	<b>1492-EBL4T-B</b>
		Yellow	50	<b>1492-EBL4T-Y</b>
0.08 x 1.37 x 4.13 in. (2 x 34.85 x 105 mm)	1492-L4Q, LG4Q	Grey	50	<b>1492-EBL4Q</b>
		Blue	50	<b>1492-EBL4Q-B</b>
		Yellow	50	<b>1492-EBL4Q-Y</b>
0.08 x 1.45 x 2.56 in. (2 x 36.95 x 65 mm)	1492-L6, LG6	Grey	50	<b>1492-EBL6</b>
		Blue	50	<b>1492-EBL6-B</b>
		Yellow	50	<b>1492-EBL6-Y</b>
0.08 x 1.45 x 3.54 in. (2 x 36.95 x 90 mm)	1492-L6T, LG6T	Grey	50	<b>1492-EBL6T</b>
		Blue	50	<b>1492-EBL6T-B</b>
		Yellow	50	<b>1492-EBL6T-Y</b>
0.12 x 1.67 x 2.89 in. (3 x 42.5 x 73.5 mm)	1492-L10, LG10	Grey	20	<b>1492-EBL10</b>
		Blue	20	<b>1492-EBL10-B</b>
		Yellow	20	<b>1492-EBL10-Y</b>
0.12 x 1.71 x 3.25 in. (3 x 43.5 x 82.5 mm)	1492-L16, LG16	Grey	20	<b>1492-EBL16</b>
		Blue	20	<b>1492-EBL16-B</b>
		Yellow	20	<b>1492-EBL16-Y</b>
—	1492-LAFB6	Black	50	<b>1492-EBLAFB6</b>
0.08 x 1.65 x 2.95 in. (2 x 41.9 x 75 mm)	1492-LD2, LDG2, LD2C, LDG2C	Grey	50	<b>1492-EBLD2</b>
		Blue	20	<b>1492-EBLD2-B</b>
		Yellow	20	<b>1492-EBLD2-Y</b>
0.08 x 1.87 x 2.85 in. (2 x 47.5 x 72.5 mm)	1492-LD3, LD3C, LDG3, LDG3C	Grey	20	<b>1492-EBLD3</b>
		Blue	20	<b>1492-EBLD3-B</b>
		Yellow	20	<b>1492-EBLD3-Y</b>
0.08 x 2.05 x 2.99 in. (2 x 52 x 76 mm)	1492-LD4, LD4C, LDG4, LDG4C, LD4DF, LD4DR, LD4RB..., LD4SS	Grey	20	<b>1492-EBLD4</b>
		Blue	20	<b>1492-EBLD4-B</b>
		Yellow	20	<b>1492-EBLD4-Y</b>