



Dimensions are not intended to be used for manufacturing purposes.  
**Note:** Height dimension is measured from top of rail to top of terminal block.

Specifications	1492-H1		1492-H2		
	<i>Finger-Safe terminal block, single-circuit, screw with pressure plate.</i>		<i>Finger-Safe terminal block, two-circuit, screw with pressure plate.</i>		
Approvals	UL / CSA / IEC		UL / CSA / IEC		
Voltage Rating	600V AC/DC		600V AC/DC		
Maximum Current	30 A		24 A		
Wire Range (Rated Cross Section)	#30...#12 AWG (0.05...4 mm <sup>2</sup> )		#30...#12 AWG (0.05...4 mm <sup>2</sup> )		
Wire Strip Length	0.38" (9.7 mm)		0.38" (9.7 mm)		
Recommended Tightening Torque	3...7 lb-in. (0.3...0.8 Nm)		3...7 lb-in. (0.3...0.8 Nm)		
Density	50 pcs./ft (164/m)		50 pcs./ft (164/m)		
Insulation Temperature Range	-40...+221°F (-40...+105°C)		-40...+221°F (-40...+105°C)		
Terminal Blocks	Cat. No.	Pcs./Pkg.	Cat. No.	Pcs./Pkg.	
Color:	White	1492-H1	80	1492-H2	50
	Two 3' Rails White	1492-H1296 (148/Rail)	1	1492-H2148 (148/Rail)	1
	Gold	1492-H1GL	80	1492-H2GL	50
	Red	1492-H1RE	80	1492-H2RE	50
	Blue	1492-H1B	80	1492-H2B	50
	Black	1492-H1BL	80	1492-H2BL	50
	Green	1492-H1G	80	1492-H2G	50
	Yellow	1492-H1Y	80	1492-H2Y	50
	Brown	1492-H1BR	80	1492-H2BR	50
	Violet	1492-H1VT	80	1492-H2VT	50
	Gray	1492-H1GY	80	1492-H2GY	50
	Orange	1492-H1OR	80	1492-H2OR	50
Accessories (page 12-172)	Cat. No.	Pcs./Pkg.	Cat. No.	Pcs./Pkg.	
Mounting Rails:					
3' Scored A-B Rail	1492-N1	20	1492-N1	20	
3' Rigid A-B Rail	1492-N22	20	1492-N22	20	
3' High Rise A-B Rail	1492-N44	2	1492-N44	2	
Standoff Brackets (use every 12")	1492-N25	2	1492-N25	2	
1 m Symmetrical DIN	—	—	—	—	
1 m Symmetrical DIN (alumin.)	—	—	—	—	
1 m Hi-Rise Symmetrical DIN	—	—	—	—	
1 m Angled Hi-Rise Sym. DIN	—	—	—	—	
End Barrier	1492-N36	50	1492-N40	50	
End Anchors:					
A-B Rail — Heavy Duty	1492-N23	10	1492-N23	10	
A-B Rail — Normal Duty	1492-N47	50	—	—	
A-B Rail — Retaining Clip — Light Duty	1492-N2	50	—	—	
DIN Rail — Normal Duty	—	—	—	—	
DIN Rail — Heavy Duty	—	—	—	—	
Side Jumpers:					
2-pole Uninsulated	1492-N42	50	1492-N42	50	
10-pole Insulated	1492-SJ6-10	10	1492-SJ6-10	10	
50-pole Uninsulated	1492-N39	10	1492-N39	10	
Side Jumper Insulating Sleeve	1492-SJS	10	1492-SJS	10	
Marking Systems	1492-N41	50	1492-N41	50	